



FWB53

FWB encl.,univers,5rows 180 mod cl.II IP44,plain door,800x800x161mm,brass term.

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	15
Number of rows	5
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	180
-------------------	-----

**Functions**

Has protection main switch	No
With conduit inlets	Yes

**Dimensions**

Height	800 mm
Width	800 mm
Depth	165 mm
Built-in height	800 mm
Built-in width	800 mm

**Cover, door**

Number of cabinet doors	2
-------------------------	---

**Dimensions**

Built-in depth	161 mm
----------------	--------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	36
-----------------------	----

**Cover, door**

Type of handle	Hinged pattern handle
Door/cover is transparent	No
Cabinet door type	Double door, asymmetric

**Connection**

Number of conduit inlets	12
--------------------------	----

**Connectivity**

Mounting type	Surface mounting
---------------	------------------

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

---

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Bar lock Without lock

---

**Sustainability**

RoHS conform	Yes
--------------	-----