



WBSH2

Technical Features

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

| | |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

| | |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

Dimensions

| | |
|------------|-------------|
| Dimensions | 77 x 117 mm |
|------------|-------------|

| | |
|----------------|-------|
| Built-in depth | 16 mm |
|----------------|-------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Texts

| | |
|-------------------|---------------------|
| Installation mode | For screw fastening |
|-------------------|---------------------|

| | |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

| | |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

| | |
|-------------|---------------------------|
| Switch mode | 2-way, with loop terminal |
|-------------|---------------------------|