



NBN463A

MCB 4P 10kA/15kA B-63A 4M

Technical Features

Electric current

| | |
|---|---------|
| Rated current | 63 A |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2 | 15 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 30 kA |
| Rated current -25°C | 78.67 A |
| Rated current at -20°C | 77.38 A |
| Rated current -15°C | 76.06 A |
| Rated current -10°C | 74.72 A |
| Rated current -5°C | 73.36 A |
| Rated current at 0°C | 71.97 A |
| Rated current 5°C | 70.56 A |
| Rated current 10°C | 69.11 A |
| Rated current 15°C | 67.64 A |
| Rated current at 20°C | 66.13 A |
| Rated current 25°C | 64.58 A |
| Rated current 30°C | 63 A |
| Rated current 35°C | 60.96 A |
| Rated current at 40°C | 58.86 A |
| Rated current at 45°C | 56.68 A |
| Rated current at 50°C | 54.40 A |
| Rated current 55°C | 52.03 A |
| Rated current 60°C | 49.55 A |
| Rated current 65°C | 46.94 A |
| Rated current 70°C | 44.17 A |

Architecture

| | |
|--------------|----|
| Type of pole | 4P |
| Curve | B |

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Main electrical attributes

| | |
|---|-------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 10 kA |
|---|-------|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

Voltage

| | |
|--------------------------------------|-------------|
| Rated operational voltage Ue | 400 - 400 V |
| Type voltage supply | AC |
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 6000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Connection

| | |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

| | |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|--|---|

| | |
|---|---|
| Class of energy limitation I ² t | 3 |
|---|---|

| | |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

Power

| | |
|---------------------------|---------|
| Total power loss under IN | 25.70 W |
|---------------------------|---------|

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 4000 |
|--|------|

| | |
|---------------------------------|-------|
| Number of mechanical operations | 20000 |
|---------------------------------|-------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

| | |
|--|------------------|
| Top connection alignment for modular devices | Aligned terminal |
|--|------------------|

| | |
|---|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|---|------------------|

Dimensions

| | |
|--------|-------|
| Height | 83 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 70 mm |
|-------|-------|

| | |
|-------|-------|
| Depth | 70 mm |
|-------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|
