



LSN503

**Fuse carrier 3P 32A 690V L38 3M**

**Technical Features**

**Dimensions**

Height	76.50 mm
Width	52.50 mm
Depth	76.90 mm

**Architecture**

Number of poles	3
-----------------	---

**Electric current**

Rated current	32 A
Rated current of fuse cartridge	0.2 A
	1 A
	2 A
	4 A
	6 A
	8 A
	10 A
	12 A
	16 A
	20 A
	25 A
	32 A

**Capacity**

Number of modules	3
-------------------	---

**Use conditions**

Operating temperature	-40 - 70 °C
-----------------------	-------------

**Installation, mounting**

Nominal tightening torque	2.20 - 2.20 Nm
Mounting on	DIN rail

**Power**

Total power loss under IN	3.50 W
---------------------------	--------

**Voltage**

Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	6000 V
Type voltage supply	AC/DC
Overvoltage category according to IEC 60947-1	3

**Safety**

Ingress Protection (IP) class	IP2X
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 16 mm <sup>2</sup>

**Fuse**

Fuse size	10 x 38
-----------	---------

**Cover, door**

Interlockable	Yes
---------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes