



LSN504

**Fuse carrier 3P+N 32A 690V L38 4M**

**Technical Features**

**Dimensions**

Height	76.50 mm
Width	70 mm
Depth	76.90 mm

**Architecture**

Number of poles	4
-----------------	---

**Electric current**

Rated current	32 A
Rated current of fuse cartridge	0.2 A 1 A 2 A 4 A 6 A 8 A 10 A 12 A 16 A 20 A 25 A 32 A

**Capacity**

Number of modules	4
-------------------	---

**Use conditions**

Operating temperature	-40 - 70 °C
-----------------------	-------------

**Installation, mounting**

Nominal tightening torque	2.20 - 2.20 Nm
Mounting on	DIN rail

**Power**

Total power loss under I <sub>N</sub>	3.50 W
---------------------------------------	--------

**Voltage**

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	6000 V
Type voltage supply	AC/DC
Overvoltage category according to IEC 60947-1	3

**Safety**

Ingress Protection (IP) class	IP2X
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 16 mm <sup>2</sup>

**Fuse**

Fuse size	10 x 38
-----------	---------

**Cover, door**

Interlockable	Yes
---------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes