



SPA180N

Combined SPD T1+T2 1P N-PE limp 100kA Uc 1.5KV remote contact integrated fuse

Technical Features

Electric current

Lightning impulse current limp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE 100 kA

Network configuration

Network type TT TN-S

Equipment

With remote signalling contact Yes

Standards

Requirement class IEC 61643 T1 T2

Capacity

Number of modules 2

Safety

Ingress Protection (IP) class IP20

Electric current

Max. discharge (Imax) L-N(PEN)/ N-PE 100 kA

Use conditions

Operating temperature -40 - 80 °C

Dimensions

Height 95.20 mm

Width 35.60 mm

Depth 67 mm

Controls and indicators

Indicator lamp Optic

Connection

Cross-section of input and output with screws, for flexible conductors 2.5 - 35 mm²

Cross-section of input and output with screws, for massive conductors 2.5 - 35 mm²

Sustainability

REACH-SVHC free Yes

RoHS conform Yes