



VME11314SPD

**13+14 Way 100A Switch Disconnecting Incomer + SM Type II SPD 2 Row**

**Technical Features**

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Architecture**

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

**Functions**

|                            |     |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection     | Yes |

**Installation, mounting**

|                            |    |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

**Configuration**

|  |   |
|--|---|
| Number of arc fault detection devices AFDD | 0 |
|--|---|

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 27 |
|-------------------|----|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

**Weight**

|        |        |
|--------|--------|
| Weight | 7.3 kg |
|--------|--------|

**Dimensions**

|        |          |
|--------|----------|
| Depth  | 102.5 mm |
| Height | 480 mm   |
| Width  | 364 mm   |

**Cover, door**

|                           |    |
|---------------------------|----|
| Interlockable             | No |
| Door/cover is transparent | No |

**Materials**

|          |       |
|----------|-------|
| RAL code | 9010  |
| Colour   | White |
| Material | Metal |

**Connection**

|                             |   |
|-----------------------------|---|
| Number of conduit inlets    | 0 |
| Number of accessible phases | 1 |

**Scope of delivery**

|  |   |
|--|---|
| Number of earth leakage circuit breaker type A | 0 |
| Number of RCCB in enclosure                    | 0 |

**Equipment**

|                        |    |
|------------------------|----|
| Number of groups       | 0  |
| Number of light groups | 0  |
| Number of rows         | 2  |
| With energy meter      | No |
| Number of rails        | 2  |
| Extension possible     | No |
| With bell transformer  | No |
| With socket outlet     | No |

**Safety**

|  |      |
|--|------|
| Impact resistance IK                   | IK05 |
| Ingress Protection (IP) class          | IP4X |
| Number of earth leakage switches 30 mA | 0    |

---

**Safety**

---

|   |   |
|---|---|
| Number of earth leakage switches 300 mA | 0 |
|---|---|

---

**Compatibility**

---

|  |    |
|--|----|
| Cooker group suitable as power current group | No |
|--|----|

---

**Sustainability**

---

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

---