



19 Way 100A Switch Disconnect Incomer Single Mod Type II SPD

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection | Yes |

Installation, mounting

| | |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

Configuration

| | |
|--|---|
| Number of arc fault detection devices AFDD | 0 |
|--|---|

Capacity

| | |
|-------------------|----|
| Number of modules | 19 |
|-------------------|----|

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 230 - 240 V |
|-----------------|-------------|

Electric current

| | |
|---------------|-------|
| Rated current | 116 A |
|---------------|-------|

Weight

| | |
|--------|--------|
| Weight | 2.8 kg |
|--------|--------|

Dimensions

| | |
|-----------------------|----------|
| Depth | 102.5 mm |
| Height | 240 mm |
| Width | 472 mm |
| Number of width units | 19 |
| Thickness of sidewall | 1 mm |

Cover, door

| | |
|---------------------------|----|
| Interlockable | No |
| Door/cover is transparent | No |

Materials

| | |
|----------|-------|
| RAL code | 9010 |
| Colour | White |
| Material | Metal |

Connection

| | |
|-----------------------------|---|
| Number of conduit inlets | 0 |
| Number of accessible phases | 1 |

Scope of delivery

| | |
|--|---|
| Number of earth leakage circuit breaker type A | 0 |
| Number of RCCB in enclosure | 0 |

Equipment

| | |
|------------------------|----|
| Number of groups | 0 |
| Number of light groups | 0 |
| Number of rows | 1 |
| With energy meter | No |
| Number of rails | 1 |
| Extension possible | No |
| With bell transformer | No |
| With socket outlet | No |

Safety

| | |
|---|-------------------|
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP4X |
| Protection class | Isolation class I |
| Number of earth leakage switches 30 mA | 0 |
| Number of earth leakage switches 300 mA | 0 |

Compatibility

| | |
|--|----|
| Cooker group suitable as power current group | No |
|--|----|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |