



dr64f4

Din rail board, 4 row 64M, non-transparent door, flush

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 415 - 415 V |
|-----------------|-------------|

Installation, mounting

| | |
|----------------------------|----------------|
| Suitable for outdoor usage | No |
| Mounting on | Flush mounting |

Power

| | |
|--|---------|
| Maximum power loss per cabinet at $\Delta T=20K$ | 30.46 W |
|--|---------|

Equipment

| | |
|----------------------------|-----|
| Number of rails | 4 |
| Number of rows | 4 |
| With lock | No |
| Has neutral terminal block | Yes |

Capacity

| | |
|---|----|
| Number of modules | 64 |
| Number of half modules terminals per rail | 32 |

Functions

| | |
|----------------------------|-----|
| Has protection main switch | No |
| With conduit inlets | Yes |

Dimensions

| | |
|-----------------|--------|
| Height | 799 mm |
| Width | 430 mm |
| Depth | 110 mm |
| Built-in height | 770 mm |
| Built-in width | 400 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

Dimensions

| | |
|----------------|--------|
| Built-in depth | 110 mm |
|----------------|--------|

Cover, door

| | |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

Dimensions

| | |
|-----------------------|----|
| Number of width units | 16 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|-------------|
| Door/cover is transparent | No |
| Cabinet door type | Single door |

Connection

| | |
|--------------------------|----|
| Number of conduit inlets | 17 |
|--------------------------|----|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9010 |
| Colour | Grey white |

Equipment

| | |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|-------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP40 |
| Locking type | Without lock |
| Glow wire test | 960 °C |
| Protection class with door | IP40 |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|