




NDN416A

### MCB 4P 10kA/15kA D-16A 4M

#### Technical Features

##### Electric current

|                                                                                               |         |
|-----------------------------------------------------------------------------------------------|---------|
| Rated current I <sub>N</sub>                                                                  | 16 A    |
| Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1 | 20 kA   |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> AC IEC 60947-2                 | 15 kA   |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2     | 15 kA   |
| Rated current -15°C                                                                           | 19.56 A |
| Rated current -10°C                                                                           | 19.20 A |
| Rated current -5°C                                                                            | 18.83 A |
| Rated current at 0°C                                                                          | 18.45 A |
| Rated current 5°C                                                                             | 18.07 A |
| Rated current 10°C                                                                            | 17.67 A |
| Rated current 15°C                                                                            | 17.27 A |
| Rated current at 20°C                                                                         | 16.86 A |
| Rated current 25°C                                                                            | 16.43 A |
| Rated current 30°C                                                                            | 16 A    |
| Rated current 35°C                                                                            | 15.48 A |
| Rated current at 40°C                                                                         | 14.94 A |
| Rated current at 45°C                                                                         | 14.38 A |
| Rated current at 50°C                                                                         | 13.80 A |
| Rated current 55°C                                                                            | 13.19 A |
| Rated current 60°C                                                                            | 12.56 A |
| Rated current 65°C                                                                            | 11.89 A |
| Rated current 70°C                                                                            | 11.18 A |

##### Architecture

|              |    |
|--------------|----|
| Type of pole | 4P |
|--------------|----|

##### Electric current

|                                                                             |         |
|-----------------------------------------------------------------------------|---------|
| Rated service breaking capacity I <sub>cs</sub> AC according to IEC 60898-1 | 7.50 kA |
|-----------------------------------------------------------------------------|---------|

##### Architecture

|       |   |
|-------|---|
| Curve | D |
|-------|---|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

##### Main electrical attributes

|                                                                                   |       |
|-----------------------------------------------------------------------------------|-------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 10 kA |
|-----------------------------------------------------------------------------------|-------|

##### Installation, mounting

|                                         |                |
|-----------------------------------------|----------------|
| Nominal tightening torque top terminal  | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque               | 2.80 - 2.80 Nm |

##### Voltage

|                                                  |        |
|--------------------------------------------------|--------|
| Type voltage supply                              | AC     |
| Rated insulation voltage U <sub>i</sub>          | 500 V  |
| Rated impulse withstand voltage U <sub>imp</sub> | 6000 V |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Connection

|                                                                        |                        |
|------------------------------------------------------------------------|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |

---

**Installation, mounting**

|                                               |                |
|-----------------------------------------------|----------------|
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |

**Safety**

|                               |       |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP20  |
| Grid distance                 | 60 mm |

**Use conditions**

|                                                          |             |
|----------------------------------------------------------|-------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2           |
| Operating temperature                                    | -25 - 70 °C |

**Power**

|                         |         |
|-------------------------|---------|
| Power dissipation at IN | 11.08 W |
|-------------------------|---------|

**Connectivity**

|                                               |                  |
|-----------------------------------------------|------------------|
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

**Dimensions**

|        |       |
|--------|-------|
| Height | 83 mm |
| Width  | 70 mm |
| Depth  | 70 mm |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|