



HWS2E312F3AE

**Air Circuit Breaker HWS2 66kA 1250A 3P Fixed LSI-AMP**

**Technical Features**

**Electric current**

Rated current	1250 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	66 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	66 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	66 kA

**Endurance**

Electric endurance in number of cycles	8000
Number of mechanical operations	12000

**Voltage**

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	12 kV
Type voltage supply	AC

**Resistance**

Internal resistance	9.3 μΩ
---------------------	--------

**Architecture**

Number of poles	3
Device construction type	Fixed built-in

**Tripping**

Time of response when closing	40 ms
-------------------------------	-------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes