



HWS4S440D3AE

**Air Circuit Breaker HWS4 85kA 4000A 4P Drawout LSI-AMP**

**Technical Features**

**Electric current**

Rated current	4000 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	85 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	85 kA
Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	85 kA

**Endurance**

Electric endurance in number of cycles	8000
Number of mechanical operations	10000

**Voltage**

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	12 kV
Type voltage supply	AC

**Resistance**

Internal resistance	13.1 μΩ
---------------------	---------

**Architecture**

Number of poles	4
Number of protected poles	4
Device construction type	Drawout
Type of pole	4P

**Tripping**

Time of response when closing	40 ms
-------------------------------	-------

**Power**

Total power loss under I <sub>N</sub>	800.1 W
---------------------------------------	---------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes