



ARM916U

### MCB with dangerous arc detection 1M 16A B curve 6kA

#### Technical Features

##### Electric current

Rated current	16 A
Rated current -25°C	20.5 A
Rated current at -20°C	20.1 A
Rated current -15°C	19.7 A
Rated current -10°C	19.3 A
Rated current -5°C	18.9 A
Rated current at 0°C	18.5 A
Rated current 5°C	18.1 A
Rated current 10°C	17.6 A
Rated current 15°C	17.2 A
Rated current at 20°C	16.8 A
Rated current 25°C	16.4 A
Rated current 30°C	16 A
Rated current 35°C	15.7 A
Rated current at 40°C	15.5 A
Rated current at 45°C	15.2 A
Rated current at 50°C	15 A
Rated current 55°C	14.7 A
Rated current 60°C	14.5 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 60898-1	6 kA

##### Architecture

Curve	B
Type of pole	1P+N

##### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

##### Installation, mounting

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

##### Voltage

Rated insulation voltage U <sub>i</sub>	400 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

##### Power

Total power loss under I <sub>N</sub>	3.8 W
---------------------------------------	-------

##### Use conditions

Class of energy limitation I <sup>2</sup> t	3
---	---

##### Endurance

Number of mechanical operations	8000
Electric endurance in number of cycles	2000

##### Installation, mounting

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

##### Capacity

Number of modules	1
-------------------	---

##### Dimensions

Height	125 mm
Width	17.50 mm
Depth	70 mm

# Product Datasheet

## ARM916U

---

### Use conditions

Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

### Sustainability

RoHS conform	Yes
--------------	-----