



ARR982U

**RCBO with dangerous arc detection 1M 32A C curve 6kA Type A 30mA**

**Technical Features**

**Electric current**

Rated current	32 A
Rated current -25°C	38.6 A
Rated current at -20°C	38 A
Rated current -15°C	37.4 A
Rated current -10°C	36.8 A
Rated current -5°C	36.2 A
Rated current at 0°C	35.6 A
Rated current 5°C	35 A
Rated current 10°C	34.4 A
Rated current 15°C	33.8 A
Rated current at 20°C	33.2 A
Rated current 25°C	32.6 A
Rated current 30°C	32 A
Rated current 35°C	31.3 A
Rated current at 40°C	30.7 A
Rated current at 45°C	30 A
Rated current at 50°C	29.3 A
Rated current 55°C	28.6 A
Rated current 60°C	28 A
Rated current 65°C	27.3 A
Rated current 70°C	26.6 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 61009-1	6 kA

**Architecture**

Curve	C
Type of pole	1P+N

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
-----------------------------------------------------------------------------------	------

**Installation, mounting**

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

**Electric current**

Breaking and opening capacity I <sub>dm</sub>	3 kA
Rated residual operating current I <sub>dn</sub>	30 mA

**Voltage**

Rated insulation voltage U <sub>i</sub>	400 V
-----------------------------------------	-------

**Safety**

Residual current type	A
-----------------------	---

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

**Power**

Total power loss under I <sub>N</sub>	9.4 W
---------------------------------------	-------

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

---

**Endurance**

Number of mechanical operations	8000
Electric endurance in number of cycles	2000

---

**Capacity**

Number of modules	1
-------------------	---

---

**Installation, mounting**

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

---

**Dimensions**

Height	125 mm
Width	17.50 mm
Depth	70 mm

---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

---

**Sustainability**

RoHS conform	Yes
--------------	-----