



ARR916U

**RCBO with dangerous arc detection 1M 16A B curve 6kA Type A 30mA**

**Technical Features**

**Electric current**

Rated current	16 A
Rated current -25°C	20.5 A
Rated current at -20°C	20.1 A
Rated current -15°C	19.7 A
Rated current -10°C	19.3 A
Rated current -5°C	18.9 A
Rated current at 0°C	18.5 A
Rated current 5°C	18.1 A
Rated current 10°C	17.6 A
Rated current 15°C	17.2 A
Rated current at 20°C	16.8 A
Rated current 25°C	16.4 A
Rated current 30°C	16 A
Rated current 35°C	15.7 A
Rated current at 40°C	15.5 A
Rated current at 45°C	15.2 A
Rated current at 50°C	15 A
Rated current 55°C	14.7 A
Rated current 60°C	14.5 A
Rated current 65°C	14.2 A
Rated current 70°C	14 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 61009-1	6 kA

**Architecture**

Curve	B
Type of pole	1P+N

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

**Electric current**

Breaking and opening capacity Idm	3 kA
Rated residual operating current Idn	30 mA

**Voltage**

Rated insulation voltage Ui	400 V
-----------------------------	-------

**Safety**

Residual current type	A
-----------------------	---

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 230 V

**Power**

Total power loss under IN	3.8 W
---------------------------	-------

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

---

**Endurance**

Number of mechanical operations	8000
Electric endurance in number of cycles	2000

**Capacity**

Number of modules	1
-------------------	---

**Installation, mounting**

Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

**Dimensions**

Height	125 mm
Width	17.50 mm
Depth	70 mm

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----