



HEQ801FR

Moulded Case Circuit Breaker h3+ PW1600 LI 4P4D 800A 70kA FTC

Technical Features

Electric current

Rated current	800 A
Rated ultimate short-circuit breaking capacity I _{cu} under 230 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 415 V AC IEC 60947-2	70 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	19.2 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	19.2 kA

Architecture

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

Tripping

Response time when opening	12 ms
----------------------------	-------

Electric current

Rated ultimate short-circuit breaking capacity I _{cu} under 690 V AC IEC 60947-2	42 kA
Rated service breaking capacity I _{cs} under 220 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I _{cs} under 240 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I _{cs} under 380 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I _{cs} under 415 V AC according to IEC 60947-2	70 kA
Rated service breaking capacity I _{cs} under 690 V AC according to IEC 60947-2	42 kA
Rated current 10°C according to IEC 60947	800 A
Rated current 15°C according to IEC 60947	800 A
Rated current 20°C according to IEC 60947	800 A
Rated current 25°C according to IEC 60947	800 A
Rated current 30°C according to IEC 60947	800 A
Rated current at 35°C according to IEC 60947	800 A
Rated current at 40°C according to IEC 60947	800 A
Rated current 45°C according to IEC 60947	800 A
Rated current 50°C according to IEC 60947	800 A
Rated current 55°C according to IEC 60947	800 A
Rated current at 60°C according to IEC 60947	800 A
Rated current 70°C according to IEC 60947	800 A
Rated current 65°C according to IEC 60947	800 A

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	50-50 Nm
Mounting-/Connection Position	Front

Voltage

Rated impulse withstand voltage U _{imp}	8 kV
Rated insulation voltage U _i	1000 V
Rated operational voltage U _e	220 - 690 V

Functions

Trip unit	Sentinel LI
-----------	-------------

Power

Total power loss under I _N	23.6 W
Power loss per pole at I _N	4.6 W

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Equipment

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Connection

Connector/plug type	Terminal
---------------------	----------

Cable

Cable material	Copper Aluminium
----------------	---------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Dimensions

Height	330 mm
Width	280 mm
Depth	198 mm

Controls and indicators

Motor drive integrated	No
------------------------	----

Compatibility

Suitable for DIN Rail	No
Compatible with RDC AOB	No
Suitable for distribution board	Yes

Power supply

Position power supply	Bidirectional
-----------------------	---------------

Connectivity

Type of connection	Bolt connection
--------------------	-----------------

Electrical protection

Long-time overload protection (ltd): delay (tr)	0.5 s
	1 s
	2 s
	4 s
	5 s
	8 s
	10 s
	15 s
	20 s
	25 s
	Instantaneous protection (li): dial setting coefficient
2	
3	
4	
6	
8	
10	
12	
15	

Sustainability

RoHS conform

Yes