



HMQ801LR

### Moulded Case Circuit Breaker h3+ PW1600 LSIG 4P4D 800A 50kA FTC

#### Technical Features

##### Electric current

|                                                                               |         |
|-------------------------------------------------------------------------------|---------|
| Rated current                                                                 | 800 A   |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 50 kA   |
| Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2 | 50 kA   |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 50 kA   |
| Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2 | 50 kA   |
| Breaking capacity on 1-pole for AC 230 V IEC 60947-2                          | 19.2 kA |
| Breaking capacity on 1-pole for AC 400 V IEC 60947-2                          | 19.2 kA |

##### Architecture

|                           |                |
|---------------------------|----------------|
| Number of poles           | 4              |
| Control/operation element | Toggle         |
| Device construction type  | Fixed built-in |
| Neutral position          | Left           |

##### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 12 ms |
|----------------------------|-------|

##### Electric current

|                                                                               |       |
|-------------------------------------------------------------------------------|-------|
| Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2 | 30 kA |
| Rated service breaking capacity Ics under 220 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 240 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 380 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 415 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 690 V AC according to IEC 60947-2   | 30 kA |
| Rated current 10°C according to IEC 60947                                     | 800 A |
| Rated current 15°C according to IEC 60947                                     | 800 A |
| Rated current 20°C according to IEC 60947                                     | 800 A |
| Rated current 25°C according to IEC 60947                                     | 800 A |
| Rated current 30°C according to IEC 60947                                     | 800 A |
| Rated current at 35°C according to IEC 60947                                  | 800 A |
| Rated current at 40°C according to IEC 60947                                  | 800 A |
| Rated current 45°C according to IEC 60947                                     | 800 A |
| Rated current 50°C according to IEC 60947                                     | 800 A |
| Rated current 55°C according to IEC 60947                                     | 800 A |
| Rated current at 60°C according to IEC 60947                                  | 800 A |
| Rated current 70°C according to IEC 60947                                     | 800 A |
| Rated current 65°C according to IEC 60947                                     | 800 A |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Installation, mounting

|                               |          |
|-------------------------------|----------|
| Nominal tightening torque     | 50-50 Nm |
| Mounting-/Connection Position | Front    |

##### Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 8 kV        |
| Rated insulation voltage Ui          | 1000 V      |
| Rated operational voltage Ue         | 220 - 690 V |

##### Functions

|           |               |
|-----------|---------------|
| Trip unit | Sentinel LSIG |
|-----------|---------------|

##### Power

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 23.6 W |
| Power loss per pole at I <sub>N</sub> | 4.6 W  |

#### Endurance

|                                        |       |
|----------------------------------------|-------|
| Electric endurance in number of cycles | 4000  |
| Number of mechanical operations        | 20000 |

#### Equipment

|                                                         |   |
|---------------------------------------------------------|---|
| Number of auxiliary contacts as change-over contact     | 0 |
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Use conditions

|                                                          |           |
|----------------------------------------------------------|-----------|
| Operating temperature                                    | -25-70 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3         |

#### Cover, door

|               |     |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

#### Cable

|                |                     |
|----------------|---------------------|
| Cable material | Copper<br>Aluminium |
|----------------|---------------------|

#### Dimensions

|        |        |
|--------|--------|
| Height | 330 mm |
| Depth  | 198 mm |

#### Controls and indicators

|                        |    |
|------------------------|----|
| Motor drive integrated | No |
|------------------------|----|

#### Compatibility

|                         |    |
|-------------------------|----|
| Suitable for DIN Rail   | No |
| Compatible with RDC AOB | No |

#### Power supply

|                       |               |
|-----------------------|---------------|
| Position power supply | Bidirectional |
|-----------------------|---------------|

#### Electrical protection

|                                                         |                                                                          |
|---------------------------------------------------------|--------------------------------------------------------------------------|
| Long-time overload protection (ltd): delay (tr)         | 0.5 s<br>1 s<br>2 s<br>4 s<br>5 s<br>8 s<br>10 s<br>15 s<br>20 s<br>25 s |
| Short-time protection (std): delay (tsd)                | 50 ms<br>100 ms<br>200 ms<br>400 ms<br>600 ms                            |
| Instantaneous protection (li): dial setting coefficient | 1.5<br>2<br>3<br>4<br>6<br>8<br>10<br>12<br>15                           |

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|