



EMERG2WA

**Emerg Test Kit Enclosed 2 NC Circuit (wired)**

**Technical Features**

**Voltage**

Command voltage for 50 Hz	230 - 230 V
---------------------------	-------------

**Dimensions**

Height	95 mm
Width	55 mm
Depth	160 mm

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Safety**

Ingress Protection (IP) class	IP30
-------------------------------	------

**Materials**

Material	Plastic
----------	---------

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Connection**

Number of contacts	2
--------------------	---

**Equipment**

Number of keys	1
----------------	---

**Capacity**

Number of modules	2
-------------------	---

**Electric current**

Rated current	25 A
---------------	------

**Compatibility**

Suitable for DIN Rail	No
-----------------------	----

**Settings**

Time delay	10 Min - 180 Min
------------	------------------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Connection**

Type of contacts	2NC
------------------	-----

**Equipment**

With lock	Yes
-----------	-----