



WNC002

IP55

Illuminated change-over switch surface-mtd, lens, W.1, grey/light grey matt LT

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey
RAL code 7011
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 76 x 76 mm
Built-in depth 0 mm
Built-in depth flush-mounted boxes 0 mm

Safety

Ingress Protection (IP) class IP55
Impact resistance IK IK08

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Installation mode For screw fastening
Type of connection With N-terminal
With plug-in terminals
Lighting With blue 230 V LED unit
For illumination
Switch mode Change-over

Sustainability

REACH-SVHC free Yes
RoHS conform Yes