



WNC003

IP55

Control change-over switch surface-mtd, lens, W.1, grey/light grey matt LT

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey
RAL code 7011
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 76 x 76 mm
Built-in depth 65 mm
Built-in depth flush-mounted boxes 0 mm

Safety

Impact resistance IK IK08
Usable in higher IP class IP55 with closed cover

Electric current

Rated current 10 A

Connection

Type of contacts 2-way
Connector/plug type Plug-in terminal
With gold-plated contacts No

Texts

Installation mode For screw fastening
Type of connection With N-terminal
With plug-in terminals
Lighting With red 230 V LED unit
For monitoring circuit
Push button No
Imprint Without imprint

Equipment

With lighting Yes

Sustainability

REACH-SVHC free Yes
RoHS conform Yes