



HWX021H

Shunt trip coil 48-60V AC/DC (SH)

Technical Features

Power

Inrush power absorbed	250 VA
Operating consumption	5 VA

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Voltage

Command voltage AC	48 - 60 V
Command voltage DC	48 - 60 V
Rated insulation voltage U_i	480 V
Rated impulse withstand voltage U_{imp}	6000 V

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes