



FWB52GS

FWB encl. univers,surface mount.,IP44,classII,w. transp.door,800x550x161mm,QC

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	10
Number of rows	5
Number of section in width	2
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	72
-------------------	----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	800 mm
Width	550 mm
Depth	165 mm
Built-in height	800 mm
Built-in width	550 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	161 mm
----------------	--------

**Cover, door**

Number of locks	1
-----------------	---

**Dimensions**

Number of width units	24
-----------------------	----

**Cover, door**

Type of handle	Latch
Door/cover is transparent	Yes
Cabinet door type	Single door

**Connection**

Number of conduit inlets	8
--------------------------	---

**Connectivity**

Mounting type	Surface mounting
---------------	------------------

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class II
------------------	--------------------

**Safety**

---

Ingress Protection (IP) class	IP44
-------------------------------	------

---

**Sustainability**

---

RoHS conform	Yes
--------------	-----

---