



FWB74N3

FWB encl.,univers,IP44,classII,240mod,interaxis 150mm,1100x1050x161mm

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 125 A

Equipment

Number of rails 22

Number of rows 22

Number of section in width 4

With lock No

Has neutral terminal block No

Capacity

Number of modules 240

Functions

With conduit inlets Yes

Dimensions

Height 1100 mm

Width 1050 mm

Depth 165 mm

Built-in height 1100 mm

Built-in width 1050 mm

Cover, door

Number of cabinet doors 2

Dimensions

Built-in depth 161 mm

Cover, door

Number of locks 1

Dimensions

Number of width units 48

Cover, door

Type of handle Hinged pattern handle

Door/cover is transparent No

Connectivity

Mounting type Surface mounting

Materials

Material Steel

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block No

Has mounting plate No

Safety

Protection class Isolation class II

Ingress Protection (IP) class IP44

Locking type Bar lock

Sustainability

RoHS conform Yes