




MSN220

MCB 2P 6kA C-10A 2M

Technical Features

Electric current

Rated current I _N	10 A
Rated short-circuit breaking capacity I _{cn} under 230 V AC according to IEC 60898-1	6 kA
Rated current at -15°C	12.8 A
Rated current at -10°C	12.5 A
Rated current at -5°C	12.2 A
Rated current at 0°C	11.9 A
Rated current at 5°C	11.6 A
Rated current at 10°C	11.3 A
Rated current at 15°C	11 A
Rated current at 20°C	10.7 A
Rated current at 25°C	10.4 A
Rated current at 30°C	10 A
Rated current at 35°C	9.8 A
Rated current at 40°C	9.5 A
Rated current at 45°C	9.2 A
Rated current at 50°C	9 A
Rated current at 55°C	8.6 A
Rated current at 60°C	8.3 A
Rated current at 65°C	8 A
Rated current at 70°C	7.7 A
Rated short-circuit breaking capacity I _{cn} under 400 V AC according to IEC 60898-1	6 kA

Architecture

Type of pole	2P
Curve	C

Capacity

Number of modules	2
-------------------	---

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	6 kA
---	------

Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage U _e	415 - 415 V
Type voltage supply	AC
Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for flexible conductors	1 - 25 mm ²
Cross-section of input with screws, for massive conductors	1 - 35 mm ²
Cross-section flexible conductor	1 - 25 mm ²
Cross-section rigid conductor	1 - 35 mm ²

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

Safety

Ingress Protection (IP) class	IP20
Grid distance	35 mm

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I ² t	3
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

Power

Power dissipation at IN	3.1 W
-------------------------	-------

Connectivity

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Type of connection	Screw terminal

Dimensions

Height	83 mm
Width	35 mm
Depth	70 mm

Sustainability

RoHS conform	Yes
--------------	-----