



WNA100



IP55

Soc.out. insert earth.pin+hinged cover surf./flushmtd,enhncd contact prot.,W1,gr

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Use conditions**

Operating temperature -15 - 30 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Grey

RAL code 7011

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Contains recycled material (% of total plastic weight) 0 %

**Dimensions**

Height 71 mm

Width 71 mm

Depth 22.80 mm

Number of units 1

Built-in depth flush-mounted boxes 0 mm

Built-in depth 22 mm

Height of P-touch band for labelling field 0 mm

**Connection**

Connector/plug type Turn screw lock

Cross-section flexible conductor without wire end sleeve 1.0 - 2.5 mm<sup>2</sup>

**Installation, mounting**

Mounting on Flush mounting  
Surface mounting

Mounting-/Connection Position Horizontal

**Connectivity**

Type of connection Plug-in connection

With claw mounting No

Mounting type Screw mounting

**Equipment**

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

**Accessories**

Has labelling field No

Pre-equipped with Socket outlet

**Cover, door**

Type of lid Self-closing hinged cover, can be arrested in end position

---

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

---

**Safety**

|                                  |     |
|----------------------------------|-----|
| With enhanced contact protection | Yes |
|----------------------------------|-----|

|                      |      |
|----------------------|------|
| Impact resistance IK | IK08 |
|----------------------|------|

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
|-------------------------------|------|

|                           |                        |
|---------------------------|------------------------|
| Usable in higher IP class | IP55 with closed cover |
|---------------------------|------------------------|

---

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
|---------------------------|----|

|                        |    |
|------------------------|----|
| With function lighting | No |
|------------------------|----|

---

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

---

**Texts**

|       |                  |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

|            |                             |
|------------|-----------------------------|
| Protection | Enhanced contact protection |
|------------|-----------------------------|

|                    |                        |
|--------------------|------------------------|
| Type of connection | With plug-in terminals |
|--------------------|------------------------|

|           |                   |
|-----------|-------------------|
| Labelling | Without labelling |
|-----------|-------------------|

---

**Suitable for**

|        |  |
|--------|--|
| cubyko |  |
|--------|--|

---

**Sustainability**

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|