



Technische Eigenschaften

Ausführung Sensor	Präsenzmelder
Erfassungswinkel	360 - 360
Erfassungswinkel horizontal	360 - 360

Stromversorgung der LED-Lampe	400 W
-------------------------------	-------

Ausschaltverzögerungszeit 0 s

Schaltschwelle	5 - 2000 lx
----------------	-------------

Einschaltverzögerungszeit	0 s
---------------------------	-----

Anschluss-/Steckertyp	Steckklemme
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
25	25
26	26
27	27
28	28
29	29
30	30
31	31
32	32
33	33
34	34
35	35
36	36
37	37
38	38
39	39
40	40
41	41
42	42
43	43
44	44
45	45
46	46
47	47
48	48
49	49
50	50
51	51
52	52
53	53
54	54
55	55
56	56
57	57
58	58
59	59
60	60
61	61
62	62
63	63
64	64
65	65
66	66
67	67
68	68
69	69
70	70
71	71
72	72
73	73
74	74
75	75
76	76
77	77
78	78
79	79
80	80
81	81
82	82
83	83
84	84
85	85
86	86
87	87
88	88
89	89
90	90
91	91
92	92
93	93
94	94
95	95
96	96
97	97
98	98
99	99
100	100

Frequenz 50 - 50 Hz

Einbautiefe	73 mm
Montagehöhe	2,50 - 2,50 m

Werkstoff	Kunststoff
Glanzgrad	Glänzend

IP-Klasse (Ingress Protection)	IP41
--------------------------------	------

Montage auf	Unterputz
Geeignet für Deckenmontage	Ja

Max. Reichweite frontal	2,50 m
Max. Reichweite zu einer Seite	5 m

REACH-SVHC frei	Ja
RoHS-konform	Ja