



XVR111C_noir

EV-Charging Station 22kW 3ph attached cable with CT 1ph one MONTA

Technical Features

Power

Power per charging point	22 kW
Connected load	0.1-22 kW

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power supply

Number of phases for power supply	3
-----------------------------------	---

Electric current

Rated current IN	32 A
------------------	------

Connectivity

Number of charging points	1
---------------------------	---

Functions

With load management	Yes
----------------------	-----

Equipment

Number of house sockets	0
With circuit breaker	No
With emergency release at power failure	Yes

Connection

Connector/plug type	Type 2S
---------------------	---------

Dimensions

Dimensions	370 x 250 mm
Height	370 mm
Width	250 mm
Depth	150 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK10

Use conditions

Operating temperature	-25 - 50 °C
-----------------------	-------------

Voltage

Nominal voltage	380-415 V
-----------------	-----------

Materials

Material	Plastic
----------	---------

Illustrations | Drawings

