



XVR111C\_noir

**EV-Charging Station 22kW 3ph attached cable with CT 1ph one MONTA**

**Technical Features**

**Power**

Power per charging point	22 kW
Connected load	0.1-22 kW

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power supply**

Number of phases for power supply	3
-----------------------------------	---

**Electric current**

Rated current	32 A
---------------	------

**Connectivity**

Number of charging points	1
---------------------------	---

**Functions**

With load management	Yes
----------------------	-----

**Equipment**

Number of house sockets	0
With circuit breaker	No
With emergency release at power failure	Yes

**Connection**

Connector/plug type	Type 2S
---------------------	---------

**Dimensions**

Dimensions	370 x 250 mm
Height	370 mm
Width	250 mm
Depth	150 mm

**Installation, mounting**

Mounting on	Wall mounting
-------------	---------------

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK10

**Use conditions**

Operating temperature	-25 - 50 °C
-----------------------	-------------

**Voltage**

Nominal voltage	380-415 V
-----------------	-----------

**Materials**

Material	Plastic
----------	---------