



SPA081

Cartridge L-N/PEN Uc 350V Iimp 25kA Up 1.5kV for SPA80X

Technical Features

Electric current

Max. discharge (I _{max}) L-N(PEN)/ N-PE	50 kA
---------------------------------------------------	-------

Network configuration

Network type	TN TT
--------------	----------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Electric current

Lightning impulse current Iimp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	25 kA
---------------------------------------------------------------------	-------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Capacity

Number of modules	2
-------------------	---

Voltage

Voltage protection level U _p according to IEC 61643-1	1.50 kV
Continuous operating voltage U _c according to IEC 61643-1	350 V
Rated operational voltage U _e	240 - 240 V
Voltage level U _p L-N/PEN IEC 61643-11	1.5 kV

Architecture

Number of poles	1
-----------------	---

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Dimensions

Height	44.8 mm
Width	35.50 mm
Depth	56.1 mm

Controls and indicators

With indicator lamp	Yes
---------------------	-----

Standards

Requirement class IEC 61643	T1 T2
-----------------------------	----------

Installation, mounting

Mounting on	Base
-------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Configuration

With integrated protection fuse	No
---------------------------------	----

Sustainability

RoHS conform	Yes
--------------	-----