



SPA801

Combined SPD T1+T2 4P Uc 350V Iimp 25kA Up 1.5kV TNS/TT with remote contact

Technical Features

Electric current

Max. discharge (Imax) L-N(PEN)/ N-PE	50 kA
--------------------------------------	-------

Network configuration

Network type	TN-S TT
--------------	------------

Electric current

Leakage-current free	Yes
Max. overcurrent protection device, parallel connection (fuse)	315 A

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Electric current

Lightning impulse current Iimp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	25 kA 100 kA
---	-----------------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Capacity

Number of modules	8
-------------------	---

Voltage

Voltage protection level Up according to IEC 61643-1	1.50 kV
Continuous operating voltage Uc according to IEC 61643-1	350 V
Rated operational voltage Ue	230 - 400 V
Voltage level Up L-N/PEN IEC 61643-11	1.5 kV

Architecture

Number of poles	4
-----------------	---

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Dimensions

Height	95.20 mm
Width	142.40 mm
Depth	67 mm

Controls and indicators

With indicator lamp	Yes
---------------------	-----

Standards

Requirement class IEC 61643	T1 T2 T3
-----------------------------	----------------

Installation, mounting

Nominal tightening torque	4.50 - 4.50 Nm
Mounting on	DIN rail

Connection

Cross-section of input and output with screws, for flexible conductors	2.5 - 35.0 mm ²
Cross-section of input and output with screws, for massive conductors	2.5 - 35.0 mm ²
Cross-section signal contact	0.14 - 1.5 mm ²

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Configuration

With integrated protection fuse	No
---------------------------------	----

Sustainability

RoHS conform	Yes
--------------	-----
