






Test Report issued under the responsibility of:



TEST REPORT IEC 60884-1 Plugs and socket-outlets for household and similar purposes Part 1: General requirements	
Report Reference No.	630003/01
Date of issue	18/01/2019
Total number of pages	52
CTF	AB Plast s.r.l – Hager Group
Address	Via dell'Artigianato 6 25080 Molinetto di Mazzano (BS) Italy
Test specification:	
Standard	IEC 60884-1:2002 (Third Edition) + A1:2006 + A2:2013
Test procedure	CB
Non-standard test method	N/A
Test Report Form No.	IEC60884_1D
Test Report Form(s) Originator	IMQ
Master TRF	Dated 2013-08
Copyright © 2013 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved. This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context. If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed. This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.	
Test item description	Adaptation Multisockets to NMP (SOCKETS FR/BE)
Trade Mark	HAGER
Manufacturer	AB Plast s.r.l
Model/Type reference	Gallery series / see general products information
Ratings	250 V~ 16 A

Responsible Testing Laboratory (as applicable), testing procedure and testing location(s):		
<input type="checkbox"/>	CB Testing Laboratory:	
Testing location/ address.....:		
Tested by (name, function, signature).....:		
Approved by (name, function, signature)....:		
<input type="checkbox"/>	Testing procedure: CTF Stage 1:	
Testing location/ address.....:		
Tested by (name, function, signature).....:		
Approved by (name, function, signature)....:		
<input checked="" type="checkbox"/>	Testing procedure: CTF Stage 2:	
Testing location/ address.....:		AB Plast s.r.l – Hager Group Via dell'Artigianato 6 25080 Molinetto di Mazzano (BS) Italy
Tested by (name + signature)		Luigi Alberti 
Witnessed by (name, function, signature) .:		Silvio Piras 
Approved by (name, function, signature)....:		Silvio Piras 
<input type="checkbox"/>	Testing procedure: CTF Stage 3:	
<input type="checkbox"/>	Testing procedure: CTF Stage 4:	
Testing location/ address.....:		
Tested by (name, function, signature).....:		
Witnessed by (name, function, signature) .:		
Approved by (name, function, signature)....:		
Supervised by (name, function, signature) :		

<p>Summary of testing:</p>	
<p>Tests performed (name of test and test clause):</p> <p>Full test program:</p> <p>All test were performed on the models WXF422B (double sockets) .</p> <p>An temperature rise test was performed on the WXF421B (single socket) to show that the tests on WXF422B (double sockets) cover the other codes</p> <p>See “General product information”.</p> <p>Specimen numbers:</p> <p>WXF422B: 18-1149; 18-1150; 18-1151; 18-1152; 18-1153; 18-1154;</p> <p>WXF421B: 18-1193; 18-1194; 18-1195;</p>	<p>Testing location:</p> <p>AB Plast s.r.l – Hager Group</p> <p>Via dell’Artigianato 6 25080 Molinetto di Mazzano (BS) Italy</p>
<p>Summary of compliance with National Differences:</p> <p>French and Belgian standard have been checked: see Appendix A at the end of this report</p> <p>Belgian standard: NBN C 61-112-1:2017,</p> <p>French standard: NF C 61-314 :2010</p>	

Copy of marking plate

- Hager logo
- Rated current & voltage
- Nature of the current
- WEEE wheeled bin logo
- Commercial code
- NF mark
- CEBEC mark



- L and N
- Earth symbol



- 12mm length
- Hager logo



Test item particulars	
Standard Sheet	I of NF C 61-314; V and I of NBN C 61-112-1 (see appendix)
Rated current (A) / Rated voltage (V)	16 / 250
Degree of protection against access to hazardous parts and against harmful ingress of solid foreign objects	IP2X
Degree of protection against harmful ingress of water	IPX0
Provision for earthing	with earthing contact
Method of connecting the cable	rewirable
Type of cable	N/A
Nominal cross-sectional areas (mm ²)	N/A
Type of terminals	screwless
Type of connections	N/A
Socket-outlets:	
Degree of protection against electric shock	normal protection
Existence of shutters	with shutters
Method of application / mounting of the socket-outlet	truncking
Method of installation	N/A
Intended for circuits where	a single earthing circuit provides protective earthing
Plugs:	
Class of equipment	0 / I / II
Possible test case verdicts:	
- test case does not apply to the test object	N/A
- test object does meet the requirement	P (Pass)
- test object does not meet the requirement	F (Fail)
Testing	
Date of receipt of test item	December 2018
Date (s) of performance of tests	December 2018 /January 2019

General remarks:

This document is issued by the company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Unless otherwise stated, the results shown in this document refer only to the sample(s) tested. This document cannot be reproduced except in full, without prior approval of the company.

The test results presented in this report relate only to the object tested.

This report shall not be reproduced, except in full, without the written approval of the Issuing testing laboratory.

"(see Enclosure #)" refers to additional information appended to the report.

"(see appended table)" refers to a table appended to the report.

Throughout this report a comma (point) is used as the decimal separator.

General product information:

New reference Gallery	Description	Color
WXF421B	Socket 2P+E 16A dedicated for trunking	White
WXF421E	Socket 2P+E 16A dedicated for trunking	Orange
WXF421N	Socket 2P+E 16A dedicated for trunking	Black
WXF421R	Socket 2P+E 16A dedicated for trunking	Red
WXF421T	Socket 2P+E 16A dedicated for trunking	Aluminium
WXF421V	Socket 2P+E 16A dedicated for trunking	Green
WXF422B	Double socket 2P+E 16A for trunking	White
WXF422E	Double socket 2P+E 16A for trunking	Orange
WXF422N	Double socket 2P+E 16A for trunking	Black
WXF422R	Double socket 2P+E 16A for trunking	Red
WXF422T	Double socket 2P+E 16A for trunking	Aluminium
WXF422V	Double socket 2P+E 16A for trunking	Green
WXF423B	Triple socket 2P+E 16A for trunking	White
WXF423E	Triple socket 2P+E 16A for trunking	Orange
WXF423N	Triple socket 2P+E 16A for trunking	Black
WXF423R	Triple socket 2P+E 16A for trunking	Red
WXF423T	Triple socket 2P+E 16A for trunking	Aluminium
WXF423V	Triple socket 2P+E 16A for trunking	Green
WXF431	Socket 2P+E 16A with detrompage dedicated for trunking	Red
WXF432	Double socket 2P+E 16A with detrompage for trunking	Red
WXF433	Triple socket 2P+E 16A with detrompage for trunking	Red

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

8	MARKING		P
8.1	Accessories marked as follows:		
	- rated current (A)	16	P
	- rated voltage (V)	250	P
	- symbol for nature of supply	~	P
	- manufacturer's or responsible vendor's name	:hager	P
	- type reference	WXF422	P
	- degree of protection (first characteristic numeral) if higher than 2.....		N/A
	- degree of protection (second characteristic numeral) if higher than 0.....		N/A
	- degree of protection (first characteristic numeral) higher than 4 for fixed socket outlet in which case the second characteristic numeral shall also be marked		N/A
	- degree of protection (second characteristic numeral) higher than 2 for fixed socket outlet in which case the first characteristic numeral shall also be marked		N/A
	Socket-outlets with screwless terminals marked with the following:		
	- the length of insulation to be removed	12mm	P
	- an indication of the suitability to accept rigid conductors only (if any)		N/A
8.2	Symbols used: as required in the standard		P
	Marking for the nature of supply placed next to the marking for rated current and rated voltage		P
8.3	Marking of fixed socket-outlets placed on the main part:		
	- rated current, rated voltage and nature of supply		P
	- identification mark of the manufacturer or of the responsible vendor		P
	- length of insulation to be removed, if any		P
	- indication of the suitability to accept rigid conductors only for screwless terminals for those socket-outlets having this restriction		N/A
	- type reference		P
	Cover plates necessary for safety purposes and intended to be sold separately: marked with the manufacturer's or responsible vendor's name and type reference		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	IP code, if applicable: marked so as to be easily discernible		N/A
	Fixed socket-outlets classified according to item b) of 7.2.5: identified by a triangle visible after installation unless they have an interface configuration different from that used in normal circuits		N/A
8.4	Plugs and portable socket-outlets: marking specified in 8.1, other than the type reference, easily discernible		N/A
	Plugs and portable socket-outlets for equipment of class II not marked with the symbol for class II construction		N/A
8.5	Neutral terminals: N	N	P
	Earthing terminals: [earth symbol]		P
	Markings not placed on screws or other easily removable parts		P
	Terminals for conductors not forming part of the main function of the socket-outlet:		
	- clearly identified unless their purpose is self-evident, or		P
	- indicated in a wiring diagram fixed to the accessory		N/A
	Identification of such terminals may be achieved by:		
	- their being marked with graphical symbols according to IEC 60417-2 or colours and/or alphanumeric system, or		P
	- their being marked with their physical dimensions or relative location		N/A
8.6	Surface-type mounting boxes forming an integral part of socket-outlets having an IP code higher than IP4X, or higher than IPX2, the IP code marked on the outside of its associated enclosure so as to be easily discernible		N/A
8.7	Indication of which position or with which special provision the declared IP of flush-type and semi-flush-type fixed socket-outlets having IP>X0 is ensured		N/A
8.8	Marking durable and clearly legible with normal or corrected vision, without additional magnification. Test: 15 s with water and 15 s with petroleum spirit		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

9	CHECKING OF DIMENSIONS		P
9.1	Accessories and surface-type mounting boxes comply with the appropriate standard sheets and corresponding gauges, if any	See ANNEX A	P
	Insertion of plugs into fixed or portable socket-outlets ensured by their compliance with the relevant standard sheets		P
	Compliance checked by measurement and by means of gauges with manufacturing tolerances as shown in table 2	See ANNEX A	P
9.2	It is not possible to engage a plug with:		
	- a socket-outlet having a higher voltage rating or a lower current rating;		P
	- a socket-outlet with a different number of live poles (exception admitted provided that no dangerous situation can arise);		P
	- a socket-outlet with earthing contact (plug for class 0 equipment).		N/A
	Engagement of a plug for class 0 or class I equipment with a socket-outlet designed to accept plugs for class II equipment, not possible		N/A
	Impossibility of insertion checked by applying a gauge, for 1 min, with a force of:		
	- 150 N (rated current ≤ 16A);		P
	- 250 N (rated current > 16A)		N/A
	Accessories with elastomeric or thermoplastic material: test carried out at (35 ± 2) °C		P
9.3	Deviations from standard sheets made only if they provide technical advantage and do not affect the purpose and safety of accessories complying with standard sheet		N/A

10	PROTECTION AGAINST ELECTRIC SHOCK		P
10.1	Socket-outlets: live parts not accessible		P
	Live parts of plugs: not accessible when the plug is in partial or complete engagement with a socket-outlet		P
	Test with test probe B of IEC 61032		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	Accessories with elastomeric or thermoplastic material: additional test carried out at (35 ± 2) °C with test probe 11 of IEC 61032 (75 N for 1 min)		P
	During the test: accessories not deform and no live parts accessible		P
	Plugs and portable socket-outlets pressed with a force of 150 N for 5 min as shown in figure 8: specimens not show deformation		N/A
10.2	Accessible parts (with exception of small screws and the like for fixing bases and covers or cover plates): made of insulating material		P
	Cover or cover plates of fixed socket-outlets and accessible parts of plugs and portable socket-outlets: made of metal if the requirements of 10.2.1 or 10.2.2 are fulfilled		P
10.2.1	Metal covers or cover plates protected by supplementary insulation made by insulating linings or insulating barriers		N/A
	Insulating linings or insulating barriers cannot be removed without being permanently damaged		N/A
	Insulating linings or insulating barriers cannot be replaced in an incorrect position and, if they are omitted, accessories are rendered inoperable or manifestly incomplete		N/A
	There is no risk of accidental contact between live parts and metal covers or cover plates		N/A
10.2.2	Metal covers or cover plates automatically connected, through a low-resistance connection, to the earth during fixing		N/A
10.3	Contact between a pin of a plug and a live socket-contact of a socket-outlet not possible while any other pin is accessible		P
	Compliance checked by manual test and by means of gauges with tolerances as specified in table 2		P
	Accessories with elastomeric or thermoplastic material: test carried out at (35 ± 2) °C		P
	Socket-outlets with enclosure or bodies of rubber or polyvinyl chloride: test carried out with a force of 75 N for 1 min		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	Fixed socket-outlets provided with metal covers or cover plates: clearance of at least 2 mm required between a pin and a socket-contact when another pin(s) is(are) in contact with the metal covers or cover plates (mm) :		N/A
10.4	External parts of plugs made of insulating material		N/A
	Overall dimensions of rings around pins not exceed 8 mm concentric with respect to the pin		N/A
10.5	Shuttered socket-outlets: live parts not accessible, without a plug in engagement, with the gauges shown in figure 9 and 10		P
	Live contacts automatically screened when the plug is withdrawn		P
	Means cannot easily be operated by anything other than a plug and not depend upon parts which are liable to be lost		P
	Gauge of figure 9, applied to the entry holes corresponding to live contacts with a force of 20 N, for approximately 5 s, successively in three directions, does not touch live parts		P
	Steel gauge of figure 10, applied to the entry holes corresponding to live contacts with a force of 1 N for approximately 5 s, in three directions, does not touch live parts		P
	Accessories with elastomeric or thermoplastic material: test carried out at $(35 \pm 2) ^\circ\text{C}$		P
10.6	Earthing contacts of a socket-outlet designed that they cannot be deformed by the insertion of a plug		P
	Test plug inserted into the socket-outlet with a force of 150 N for 1 min		P
10.6	Earthing contacts of a socket-outlet designed that they cannot be deformed by the insertion of a plug		P
	After this test: socket-outlet still comply with the requirements of clause 9		P
10.7	Socket-outlet with increased protection: live parts not accessible		N/A
	Test wire of 1 mm diameter (figure 10) applied with a force of 1 N on all accessible surfaces does not touch live parts		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	Accessories with elastomeric or thermoplastic material: test carried out at (35 ± 2) °C		N/A
11	PROVISION FOR EARTHING		P
11.1	Earth connection made before the current-carrying contacts of the plug become live		P
	Current-carrying pins are separated before the earth connection is broken		P
11.2	Earthing terminals of rewirable accessories comply with clause 12		P
	Earthing terminals of the same size as the corresponding terminals for the supply conductors		P
	Earthing terminals of rewirable accessories: internal		P
	Earthing terminals of fixed socket-outlets: fixed to the base or to a part reliably fixed to the base		P
	Earthing contacts of fixed socket-outlets:		
	- fixed to the base, or		P
	- fixed to the cover (reliably connected to the earthing terminals; contact pieces silver plated or with adequate protection)		N/A
	Parts of earthing circuit in one piece or reliably connected by riveting, welding, or the like		P
11.3	Accessible metal parts of fixed socket-outlets: permanently and reliably connected to the earthing terminal		P
11.4	Socket-outlets, having an IP>X0, with enclosure of insulating material and more than one cable inlet, provided with:		
	- an internal fixed earthing terminal, or		N/A
	- adequate space for a floating terminal (test connection using the type of terminal specified by the manufacturer), unless		N/A
	- earthing terminal of socket-outlet itself allows the connection of an incoming and an outgoing earthing conductor		N/A
11.5	Connection between earthing terminal and accessible metal parts: of low resistance		P
	Test current equal to 1,5 times the rated current or 25 A (A)	25	—
	Resistance not exceed 0,05 Ω (Ω)	0,006	P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

11.6	Fixed socket-outlets according to item b) of 7.2.5: earthing socket contact and its terminal electrically separated from any metal mounting means or other exposed conductive parts which may be connected to the protective earthing circuit of the installation		N/A
------	---	--	-----

12	TERMINALS AND TERMINATIONS		P
	All the test on terminals, with the exception of the tests of 12.3.11 and 12.3.12, made after the test of clause 16		P
12.1	General		P
12.1.1	Rewirable fixed socket-outlets provided with screw-type terminals or with screwless terminals	SCREWLESS	P
	Rewirable plugs and portable socket-outlets provided with terminals with screw clamping		N/A
	Pre-soldered flexible conductors used: pre-soldered area outside the clamp area of screw-type terminals		N/A
	Clamping means of terminals: not serve to fix any other components		P
12.1.2	Non-rewirable accessories provided with soldered, welded, crimped or equally effective permanent connections (termination)		N/A
	Screwed or Snap-On connections not used		N/A
	Connections made by crimping a pre-soldered flexible conductor not permitted		N/A
12.2	Terminals with screw clamping for external copper conductors		N/A
12.2.1	Accessories provided with terminals which allows the proper connection of copper conductors as shows in table 3		N/A
	Rated current (A); Type of accessories		—
	Type of conductor (rigid / flexible)		—
	Smallest / largest cross-sectional area (mm ²)		—
	Diameter of the largest conductor (mm)		—
	Figure of terminal		—
	Minimum diameter D (minimum dimensions) of conductor space: required (mm); measured (mm) :		
12.2.2	Terminals allow the conductor to be connected without special preparation		N/A
12.2.3	Terminals have adequate mechanical strength		N/A
	Screws and nut for clamping the conductors have metric ISO thread or a comparable thread		

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	Screws not of soft metal such as zinc or aluminium		
12.2.4	Terminals resistant to corrosion		N/A
12.2.5	Terminals clamp the conductor(s) without undue damage	See appended table 12.2.5	N/A
	During the test: conductor not slip out, no break near clamping unit and no damage		
12.2.6	Terminals clamp the conductor reliably between metal surfaces	See appended table 12.2.6	N/A
	During the test: conductor not move noticeably		
12.2.7	Terminals designed or placed that the conductor cannot slip out while the clamping screws or nuts are tightened	See appended table 12.2.7	N/A
	After the test: no wire of the conductor escaped from the clamping unit		
12.2.8	Terminals not work loose from their fixing to accessories		N/A
	Torque test (screws and nuts tightened and loosened 5 times):		
	- rated current (A)		—
	- copper conductor of the largest cross-sectional area (mm ²) (table 3)		—
	- type of conductor (solid or stranded)		—
	- torque (Nm) (table 6 or appropriate figures 2, 3 or 4)		—
	During the test: terminals not work loose and show no damage		
12.2.9	Clamping screws or nuts of earthing terminals: adequately locked against accidental loosening, not possible to loosen them without the aid of a tool		N/A
12.2.10	Earthing terminals: no risk of corrosion		N/A
	Body of brass or other metal no less resistant to corrosion		
	The body is a part of a frame or enclosure of aluminium alloy: precautions are taken to avoid the risk of corrosion		
12.2.11	Pillar terminals: distance <i>g</i> no less than the value specified in figure 2: required (mm); measured (mm)		N/A
	Mantle terminals: distance <i>g</i> no less than the value specified in figure 5: required (mm); measured (mm)		
12.3	Screwless terminals for external copper conductors		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

12.3.1	Screwless terminals of the type suitable for:		
	- for rigid copper conductors only, or		N/A
	- for both rigid and flexible copper conductors (tests carried out with rigid and then repeated with flexible conductors)		P
12.3.2	Screwless terminals provided with two clamping units each allowing the proper connection of rigid or of rigid and flexible conductors having nominal cross-sectional areas from 1,5 up to 2,5 mm ² (table 7)		P
	Two conductors to be connected: each conductor introduced in a separate clamping unit		P
12.3.3	Screwless terminals allow the conductor to be connected without special preparation		P
12.3.4	Parts of screwless terminals intended for carrying current of materials as specified in 26.5		P
12.3.5	Screwless terminals clamp specified conductors with sufficient contact pressure without undue damage to the conductor		P
	Conductor clamped between metal surfaces		P
12.3.6	It is clear how the connection and disconnection of the conductors is to be made		P
	Disconnection of a conductor require an operation, other than a pull, so that can be made manually with or without a general-purpose tool		P
	It is not possible to confuse the opening intended for the use of a tool with the opening intended for the conductor		P
12.3.7	Screwless terminals intended for the interconnection of two or more conductors:		
	- the clamping of one of the conductors is independent of the clamping of the other conductor(s)		P
	- during the connection or disconnection the conductors can be connected or disconnected either at the same time or separately		P
	- each conductor introduced in a separate clamping unit.		P
	- it is possible to clamp securely any number of conductors up to the maximum as designed. Number of conductors; Nominal cross-sectional area (mm ²) : 2; 2,5		P
12.3.8	Screwless terminals of fixed socket-outlets: adequate insertion obvious and over-insertion prevented		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

12.3.9	Screwless terminals properly fixed to the socket-outlets		P
	Not work loose when conductors are connected or disconnected		P
	Self-hardening resins used to fix terminals not subject to mechanical stress		P
12.3.10	Screwless terminals withstand mechanical stresses occurring in normal use	See appended table 12.3.10	P
	During application of the pull conductor not come out of the terminal		P
	Additional test with apparatus shown in figure 11	See appended table 12.3.10	P
	During the test: conductors not moved noticeably in the clamping unit		P
	After these tests: neither terminals nor clamping means have worked loose and conductors show no deterioration		P
12.3.11	Screwless terminals withstand electrical and thermal stresses occurring in normal use	See appended table 12.3.11	P
	After the test: inspection show no changes		P
	Repetition of mechanical strength test according to 12.3.10	See appended table 12.3.11	P
	During application of the pull conductor not come out of the terminal		P
	Additional test with apparatus shown in figure 11	See appended table 12.3.11	P
	During the test: conductors not moved noticeably in the clamping unit		P
	After these tests: neither terminals nor clamping means have worked loose and conductors show no deterioration		P
12.3.12	Screwless terminals: connected rigid solid conductor remains clamped, even when deflected during normal installation	See appended table 12.3.12	P

13	CONSTRUCTION OF FIXED SOCKET-OUTLETS		P
13.1	Socket-contact assembly have sufficient resilience to ensure adequate contact pressure on plug pins		P
	Part of socket-contact assembly ensure metallic opposing contacts at least on two sides of each pins		P
13.2	Socket-contact and pin(s) of socket-outlet which are made of copper or copper alloy, as specified in 26.5, are considered as complying with this requirement		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	The pin(s) of socket-outlets so constructed in such a way that the mechanical strength of the pin(s) does not depend on the plastic material		P
	Compliance is checked by inspection and in case of doubt by the tests of 14.2 and Clause 21 on a new set of specimens without plastic		P
13.3	Insulating linings, barriers and the like: adequate mechanical strength		P
13.4	Socket-outlets constructed as to permit		
	- easy introduction into the terminal and reliable connection of the conductors in the terminals, except for lead wires of pilot lights		P
	- easy fixing of the main part to a wall or in a mounting box		P
	- correct positioning of the conductors		P
	- adequate space between the underside of the main part and the surface on which the main part is mounted;		P
	- adequate space between the sides of the main part and the enclosure (cover or box);		P
	Socket-outlets having screwless terminals, constructed that the connecting and/or disconnecting means of the screwless terminals cannot be activated by the conductors during and after installation		P
	Compliance is checked by inspection and in case of doubt by the following test		
	The test is carried out with a solid copper conductor having the smallest cross-sectional area, as specified in 12.3.2. (mm ²).....:	1,5	P
	If it is not possible to exert a force onto the connecting/disconnecting device, the product is deemed to comply with the requirements without further tests.		P
	During the application of the pull, the conductor do not come out of the screwless terminal		P
	In addition socket-outlets classified as design A: permit easy positioning and removal of the cover or cover plate, without displacing the conductors or activating the connecting and/or disconnecting means of screwless terminals.		P
	Compliance is checked by inspection and by an installation test with conductors of the largest nominal cross-sectional area specified in Table 3 (mm ²).....:	2,5	P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
13.5	Socket-outlets designed that full engagement of associated plugs is not prevented by any projection from their engagement face		P
	Gap between the engagement face of the socket-outlet and the plug: not exceed 1 mm		P
13.6	Covers provided with bushings for the entry holes for the pins: not possible to remove them from the outside or for them to become detached inadvertently from the inside when the cover is removed		N/A
13.7	Covers, cover-plates or parts of them intended to ensure protection against electric shock:		
	- held in place at two or more points by effective fixings		P
	- fixed by means of a single fixing, for example, by a screw, provided that they are located by another means (for example, by a shoulder)		N/A
	Fixings of covers or cover-plates of socket-outlets of design A serve to fix the main parts: there are means to maintain the base in position, even after removal of the covers or cover-plates		P
13.7.1	Covers or cover-plates whose fixings are of the screw-type:		N/A
	Compliance checked by inspection only		N/A
13.7.2	Covers or cover-plates whose fixing is not dependent on screws and whose removal is obtained by applying a force in a direction approximately perpendicular to the mounting/supporting surface:		
	Compliance checked, when their removal may give access, with the standard test finger:		
	to live parts: by the test of 24.14 (verification of the non-removal and the removal)		N/A
	to non-earthed metal parts separated from live parts in such a way that creepage distances and clearances have the values shown in table 23: by the test of 24.15 (verification of the non-removal and the removal)		N/A
	only to parts of insulating material, or earthed metal parts, or metal parts separated from live parts in such a way that creepage distances and clearances have twice the values shown in table 23, or live parts of SEL V circuits not greater than 25 V a.c.: by the test of 24.16 (verification of the non-removal and the removal)		N/A
13.7.3	Covers or cover-plates the fixing of which is not dependent on screws and whose removal is obtained by using a tool, in accordance with the manufacturer's instructions given in an instruction sheet or in other documentation:		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	Compliance checked, when their removal may give access, with the standard test finger:		
	to live parts: by the test of 24.14 (verification of the non-removal only)		
	to non-earthed metal parts separated from live parts in such a way that creepage distances and clearances have the values shown in table 23: by the test of 24.15 (verification of the non-removal only)		
	only to parts of insulating material, or earthed metal parts, or metal parts separated from live parts in such a way that creepage distances and clearances have twice the values shown in table 23, or live parts of SEL V circuits not greater than 25 V a.c.: by the test of 24.16 (verification of the non-removal only)		
13.8	Cover-plate intended for a socket-outlet with earthing contact: not interchangeable with a cover-plate intended for a socket-outlet without earthing contact		P
13.9	Surface-type socket-outlets: no free openings in their enclosures		N/A
13.10	Screws or other means for mounting the socket-outlet on a surface in a box or enclosure: easily accessible from the front		P
	Fixing means not serve any other fixing purpose		P
13.11	Multiple socket-outlets with a common base: provided with fixed links for the interconnection of the contacts in parallel		P
	Fixing of the links independent from the connection of the supply wires		P
13.12	Multiple socket-outlets, comprising separate bases: correct position of each base ensured		N/A
	Fixing of each base independent of the fixing of the combination to the mounting surface		N/A
13.13	Mounting plate of surface-type socket-outlets: adequate mechanical strength		N/A
13.14	Socket-outlets withstand the lateral strain imposed by equipment likely to be introduced into them		P
	Socket-outlets 16A 250V: test made 4 times with the socket-outlet turned through 90°, 5 N for 1 min (device shown in fig. 13)		P
	During the test: device not become disengaged from the socket-outlet		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	After the test:		
	- no damage		P
	- socket-outlets comply with clause 22		P
13.15	Socket-outlets are not an integral part of lampholders		P
13.16	Surface-type socket-outlets having IP>20 are according to their IP classification when fitted with conduits or with sheathed cables and without a plug in engagement		N/A
	Surface-type socket-outlets having IPX4 and IPX6 have provision for opening a drain hole		N/A
	Socket-outlets with a drain hole: drain hole is not less than 5 mm in diameter, or 20 mm ² in area with a width and a length of not less than 3 mm		N/A
	Drain hole: effective		N/A
	Lid springs (if any): of corrosion-resistant material (bronze or stainless steel)		N/A
13.17	Earthing pins: adequate mechanical strength		P
	Not solid pins: compliance checked by inspection and by the test of 14.2 made after the tests of clause 21		P
13.18	Earthing contacts, phase contacts and neutral contacts :		
	- locked against rotation;		P
	- when the product is ready for the wiring do not possible to be removed without the use of a tool		P
13.19	Metal strips of the earthing circuit: no burrs which might damage the insulation of the supply conductors		P
13.20	Socket-outlets to be installed in a box: designed that the conductor ends can be prepared after the box is mounted in position, but before the socket-outlet is fitted in the box		P
13.21	Inlet openings: allow the introduction of the conduit or the sheath of the cable		P
	Surface-type socket-outlets:		N/A
	the conduit or sheath of the cable can enter at least 1 mm into the enclosure		N/A
	inlet opening for conduit entries, or at least two of them if there are more than one, capable of accepting conduit sizes of 16, 20, 25 or 32 according to IEC 60423 or a combination of at least two of any of these sizes		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	inlet opening for cable entries capable of accepting cables having the dimensions specified in table 14 or be as specified by the manufacturer: rated current (A); Limits of external dimensions of cable min/max (mm)		N/A
13.22	Membranes (grommets) in inlet openings: reliably fixed and not displaced by the mechanical and thermal stresses occurring in normal use		N/A
	Test on membranes subjected to the ageing treatment specified in 16.1 and assembled in the accessories		N/A
	Accessories placed at (40 ± 2) °C for 2 h. Force of 30 N applied for 5 s by test probe 11 of IEC 61032. During the test: no deformation		N/A
	Membranes likely to be subjected to an axial pull: axial pull of 30 N applied for 5 s. During the test: membranes not become detached		N/A
	After the test: no harmful deformation, cracks or similar damage		N/A
	Test repeated with membranes not subjected to any treatment		N/A
13.23	Membranes in inlet openings: introduction of the cables into the accessory permitted when the ambient temperature is low		N/A
	Test on membranes not subjected to the ageing treatment specified in 16.1 and assembled in the accessories		N/A
	Accessories kept at (-15 ± 2) °C for 2 h: possibility to introduce cables of the largest diameter through membranes		N/A
	After the test: no harmful deformation, cracks or similar damage		N/A

14	CONSTRUCTION OF PLUGS AND PORTABLE SOCKET-OTLETS		N/A
14.1	Non-rewirable portable accessories:		N/A
	flexible cable cannot be separated from the accessory without making it permanently useless		N/A
	Accessory cannot be opened by hand or by using a general purpose tool, for example a screwdriver used as such		N/A
14.2	Pins of portable accessories: adequate mechanical strength		N/A
	Test for pins not solid (made after clause 21): force of 100 N exerted on the pin, according to figure 14, for 1 min by means of a steel rod Ø 4,8 mm		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	During the application of the force: reduction of the dimension of the pin not exceed 0,15 mm		N/A
	After removal of the rod: dimensions of the pin not changed by more than 0,06 mm		N/A
14.3	Pins of plugs:		N/A
	- locked against rotation		N/A
	- not removable without dismantling the plug		N/A
	- adequately fixed in the body of the plug when the plug is wired and assembled as in normal use		N/A
	Earthing or neutral pins or contacts of plugs: not possible to arrange in an incorrect position		N/A
14.4	Earthing contacts and neutral contacts of portable socket-outlets:		N/A
	- locked against rotation		N/A
	- removable only with the aid of a tool, after dismantling the socket-outlet		N/A
14.5	Socket-contact assemblies: sufficient resilience		N/A
	Parts of socket-contact assemblies:		N/A
	- are not of insulating material except ceramic, or other material with no less suitable characteristics		N/A
	- ensure metallic contacts at least on two opposing sides of each pin		N/A
	Contact pressure of the contact tube does not depend on soldered connection only		N/A
14.6	Pins and socket-contacts: resistant to corrosion and abrasion		N/A
14.7	Enclosures of rewirable portable accessories: completely enclose terminals and ends of flexible cable		N/A
	Construction of rewirable accessories:		N/A
	- conductors can be properly connected		N/A
	- cores not pressed against each other		N/A
	- cores of live conductor not pressed against accessible metal parts		N/A
	- core of earthing conductor not pressed against live parts		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
14.8	Rewirable portable accessories: terminal screws or nuts cannot become loose and fall out of position and establish an electrical connection between live parts and earthing terminal or metal parts		N/A
14.9	Rewirable portable accessories with earthing contact: ample space for slack of earthing (test)		N/A
	Non-rewirable non-moulded-on accessories with earthing contact: current-carrying conductors stressed before the earthing conductor if the flexible cable slips in its anchorage		N/A
14.10	Terminals of rewirable portable accessories and terminations of non-rewirable portable accessories: located and shielded that loose wires not present a risk of electric shock		N/A
	Non-rewirable moulded-on portable accessories: provided with means to prevent loose wires of a conductor from reducing the minimum isolation distance requirements		N/A
14.10.1	Rewirable accessories: test with 6 mm free wire		N/A
	free wire of a conductor connected to a live terminal not touch any accessible metal part or able to emerge from the enclosure		N/A
	free wire of a conductor connected to an earthing terminal not touch a live part		N/A
14.10.2	Non-rewirable, non-moulded-on accessories: test with a free wire of length equivalent to the maximum designed stripping length declared by the manufacturer plus 2 mm		N/A
	free wire of a conductor connected to a live termination not touch any accessible metal part or reduce creepage distance and clearance below 1,5 mm to the external surface		N/A
	free wire of a conductor connected to an earth termination not touch any live part		N/A
14.10.3	Non-rewirable, moulded-on accessories:		N/A
	Verification of means to prevent stray wires reducing the minimum distance through insulation to external accessible surface below 1,5 mm		N/A
14.11	Rewirable portable accessories:		N/A
	- clear how relief from strain and prevention of twisting is intended to be effected		N/A
	- cord anchorage, or at least part of it, integral with or fixed to one of the component parts of the plug or portable socket-outlet		N/A
	- makeshift methods not used		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	- cord anchorage suitable for the different types of flexible cable which may be connected to it; screws, if any: not serve to fix any other component		N/A
	- cord anchorages: of insulating material or provided with an insulating lining fixed to the metal parts		N/A
	- metal parts of cord anchorages, including clamping screws: insulated from the earthing circuit		N/A
14.12	Rewirable portable accessories and non-rewirable non-moulded on portable accessories: it is not possible to remove covers, cover-plates or parts of them intended to ensure protection against electric shock without the use of a tool		N/A
14.13	Covers of portable socket-outlets: bushings for entry holes for the pins not removable from the outside or detachable inadvertently from the inside		N/A
14.14	Screws intended to allow access to interior of the accessory: captive		N/A
14.15	Engagement face of plugs: no projections		NA
14.16	Engagement face of portable socket-outlets: no projection		N/A
14.17	Portable accessories of IP>20: enclosed according to their IP classification		N/A
	Plugs having IP>20: adequately enclosed with the exception of the engagement face		N/A
	Portable socket-outlets having IP>20: adequately enclosed without a plug in engagement		N/A
	Lid springs (if any): of corrosion-resistant material (bronze or stainless steel)		N/A
14.18	Portable socket-outlets: means for suspension from a wall or other mounting surfaces not allow access to live parts		N/A
	No free openings between space intended for suspension means by which the socket-outlet is fixed to the wall, or other mounting surface and live parts		N/A
14.19	Combinations of portable accessories and switches, circuit-breakers or other devices comply with relevant individual IEC standards, if relevant combined product standard does not exist		N/A
14.20	Portable accessories: not integral part of lampholders		N/A
14.21	Plugs for equipment of class II:		N/A
	- rewirable or non-rewirable		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	- if part of a cord set: provided with a connector for equipment of class II		N/A
	- if part of a cord extension set: provided with a portable socket-outlet for equipment of class II		N/A
14.22	Components (switches and fuses) incorporated in accessories: comply with the relevant IEC standard		N/A
14.23	Plug-in equipment: not cause overheating of the pins or impose undue strain		N/A
	Plugs with rating above 16 A and 250 V: not integral part of other equipment		N/A
	Tests for two-pole plugs, with or without earthing contact, with rating up to and including 16 A and 250 V (plug of equipment inserted into a fixed socket-outlet complying with this standard):		N/A
14.23.1	Socket-outlet connected to a supply voltage equal to 1,1 times the highest rated voltage of the equipment (V)		—
	Temperature rise of the pins after 1 h not exceed 45 K (K)		N/A
14.23.2	Additional torque applied to the socket-outlet in order to maintain the engagement face in the vertical plane not exceed 0,25 Nm (Nm)		N/A
14.24	Plugs can easily withdrawn by hand from the relevant socket-outlets		N/A
	Gripping surfaces are so designed that the plug can be withdrawn without having to pull the flexible cable		N/A
14.25	Membranes in inlet openings of portable accessorie: meet the requirements of 13.22 and 13.23		N/A

15	INTERLOCKED SOCKET-OUTLETS		N/A
	Socket-outlet interlocked with a switch:		N/A
	plug cannot be inserted into or completely withdrawn from the socket-outlet while the socket-contacts are live		N/A
	socket-contacts cannot be made live until a plug is almost completely in engagement		N/A

16	RESISTANCE TO AGEING, PROTECTION PROVIDED BY ENCLOSURES, AND RESISTANCE TO HUMIDITY		P
16.1	Resistance to ageing		P
	Accessories are resistant to ageing		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	For accessories having a lid, the lid is closed during the test		N/A
	Portable socket-outlets: the plug of the same system having the same rated current as the socket-outlet inserted into the socket-outlet during the test		N/A
	Accessories subjected to a test in a heating cabinet at (70 ± 2) °C for seven days (168 h)		P
	After the tests, the specimens show:		
	- no crack visible with normal or corrected vision without additional magnification		P
	- no sticky or greasy material		P
	- no trace of cloth (forefinger pressed with 5 N)		P
	- no damage		P
	Portable socket-outlets: contact pressure of the contact assembly checked as specified in subclause 22.2 with the single-pin gauge		N/A
16.2	Protection provided by enclosures		
	Enclosures provide a degree of protection in accordance with the IP designation of the accessory		P
16.2.1	Protection against access to hazardous parts and against harmful effects due to ingress of solid foreign objects		
	Accessories and their enclosures provide a degree of protection against access to hazardous parts and against harmful effects due to ingress of solid foreign objects		P
	Fixed socket-outlets: mounted as in normal use on a vertical surface		P
	Flush-type and semi-flush type socket-outlets: mounted in an appropriate box according to the manufacturer's instructions		P
	Accessories with screwed glands or membranes fitted with flexible cables within the range specified in table 3:		
	- largest cross-sectional area (mm ²); type of cable (table 17)	2,5	—
	- smallest cross-sectional area (mm ²); type of cable (table 17)	1,5	—
	Glands tightened with a torque equal to 2/3 of the torque applied during the test of 24.6 (Nm)		—
	Screws of the enclosure tightened with a torque equal to 2/3 of the torque given in table 6 (Nm) ..		—

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

16.2.1.1	Protection against access to hazardous parts		
	Appropriate test performed as specified in IEC 60529 (see also clause 10)		P
16.2.1.2	Protection against harmful effects due to ingress of solid foreign objects		
	Appropriate test performed as specified in IEC 60529		P
	Test on accessories with IP5X (considered to be of category 2): dust not penetrated in a quantity to interfere with satisfactory operation or to impair safety		N/A
	Test on accessories with IP6X (considered to be of category 1): dust do not penetrate		N/A
16.2.2	Protection against harmful effects due to ingress of water		N/A
	Accessories and their enclosures provide a degree of protection against harmful effects due to ingress of water in accordance with their IP classification		N/A
	Appropriate test performed as specified in IEC 60529 under the following conditions:		
	Flush-type and semi-flush type socket-outlets: fixed in a vertical test wall using an appropriate box according to the manufacturer's instructions		N/A
	Accessory suitable to be installed on a rough wall: test wall according to figure 15 is used		
	Surface-type socket-outlets mounted as for normal use in a vertical position and fitted with cables (having conductors of the largest and smallest nominal cross-sectional area given in table 3) or conduits or both in accordance with the manufacturer's instructions:		N/A
	- largest cross-sectional area (mm ²); type of cable (table 17)		—
	- smallest cross-sectional area (mm ²); type of cable (table 17)		—
	Portable socket-outlets tested on a plain, horizontal surface in a position as in normal use and fitted with flexible cables (having conductors of the largest and smallest nominal cross-sectional area given in table 3) according to table 17:		N/A
	- largest cross-sectional area (mm ²); type of cable (table 17)		—
	- smallest cross-sectional area (mm ²); type of cable (table 17)		—
	Screws of enclosure tightened with a torque equal to 2/3 of the torque given in table 6 (Nm)		—
	Glands tightened with a torque equal to 2/3 of the torque applied during the test of 24.6 (Nm)		—

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	Accessory with drain holes opened during the test: any accumulation of water proved by inspection		N/A
	Socket-outlets tested without a plug in engagement		N/A
	Plugs tested when in full engagement with:		
	- a fixed socket-outlets		N/A
	- a portable socket-outlets		N/A
	of the same system and with the same degree of protection against harmful effects due to ingress of water		—
	Specimens withstand an electric strength test specified in 17.2 which is started within 5 min of completion of the IP test		N/A
16.3	Resistance to humidity		P
	Accessories proof against humidity which may occur in normal use		P
	Compliance checked by a humidity treatment carried out in a humidity cabinet containing air with relative humidity maintained between 91 % and 95 %		P
	Specimens kept in the cabinet for:		
	- two days (48 h) for accessories having IPX0		P
	- seven days (168 h) for accessories having IP>X0		N/A
	After this treatment the specimens show no damage		P

17	INSULATION RESISTANCE AND ELECTRIC STRENGTH		P
17.1	Insulation resistance measured 1 min after application of 500 V d.c.	See appended table 17.1	P
17.2	Electric strength: a.c. test voltage applied for 1 min	See appended table 17.2	P

18	OPERATION OF EARTHING CONTACTS		P
	Earthing contacts provide adequate contact pressure and not deteriorate in normal use		P
	Compliance checked by the tests of clauses 19 and 21		P

19	TEMPERATURE RISE		P
	Accessories constructed that they comply with the following temperature rise test		P
	Non-rewirable accessories are tested as delivered		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	In the case of multiple socket-outlets, the test is carried out on one socket-outlet of each type and current rating with the test current as specified in Table 20 passed through that one socket-outlet	See appended tables	P
	The temperature rise of the terminals, terminations and clamping units according to Figure 44 determined by means of thermocouples do not exceed 45 K	See appended tables	P
19.1	Socket-outlets and plugs are tested as follows:		
	Socket-outlets tested using a test plug with brass pins having the minimum specified dimensions	See appended table 19.1	P
	For this test the temperature rise is measured on the terminals and terminations.		P
	Plugs tested with clamping units having dimensions specified in Figure 44 fitted on each live pin and earthing pin, if any	See appended table 19.1	N/A
	Plugs having lateral earthing contacts and resilient earthing contacts tested using a fixed socket-outlet complying with the standard and having as near to-average characteristics as can be selected, but with minimum size of the earthing pin, if any	See appended table 19.1	N/A
19.2	Fixed socket-outlets of a socket-outlet and fused plug system are tested as follows:		N/A
	a) For a single socket-outlet the plug is inserted into the socket-outlet and 70 % of the test current is passed through the plug	See appended table 19.2	N/A
	The balance of the total test current is passed, simultaneously through a looped connection, connected to the socket-outlet terminals		N/A
	The total nominal load on the supply cable is passed for 60 min	See appended table 19.2	N/A
	b) For a multiple socket-outlet a plug is inserted into one socket-outlet and 70 % of the test current is passed	See appended table 19.2	N/A
	A second plug is inserted into another socket-outlet and the balance of the total test current is passed simultaneously through this plug.....:	See appended table 19.2	N/A
	The total nominal load on the supply cable is passed for 60 min.	See appended table 19.2	N/A
19.3	Portable socket-outlets and rewirable plugs with incorporated components are tested by the following two tests:		N/A
	– with a current which is equal to the test current as indicated in Table 20, for Clause 19	See appended table 19.3	N/A
	– with a current which is equal to the rated current of the portable accessory or the rated current of the component(s), whichever is the lower	See appended table 19.3	N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	Non-rewirable plugs with incorporated components are tested by the following two tests:		N/A
	– with a current which is equal to the test current for the combination of the plug and the cable as indicated in Table 20, for Clause 19	See appended table 19.3	N/A
	– with a current which is equal to the test current for the combination of the plug and the cable as indicated in Table 20, for Clause 21, or the rated current of the component(s), whichever is the lower	See appended table 19.3	N/A

20	BREAKING CAPACITY		P
	Accessories have adequate breaking capacity		P
	Compliance checked by testing:		
	- socket-outlets;	See appended table 20	P
	- plugs with pins which are not solid	See appended table 20	N/A
	Multiple socket-outlets: test carried out on one socket-outlet of each type and current rating		P
	During the test: no sustained arcing occur		P
	After the test:		
	- specimens show no damage impairing their further use;		P
	- entry holes for the pins not show any damage which may impair the safety		P

21	NORMAL OPERATION		P
	Accessories withstand without excessive wear or other harmful effect, the mechanical, electrical and thermal stresses occurring in normal use		P
	Compliance checked by testing:		
	- socket-outlets;	See appended table 21	P
	- plugs with resilient earthing socket-contacts;	See appended table 21	N/A
	- plugs with pins which are not solid	See appended table 21	N/A
	Test performed according to the procedure specified in Figure 43; point of Figure 43 at which the test program has begun (1, 2, 3)		—
	Test current passed:		
	- during each insertion and withdrawal of the plug (In ≤ 16A)		P
	- during alternate insertion and withdrawal, the other insertion and withdrawal being made without current flowing (In > 16A)		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	Multiple socket-outlets: test carried out on one socket-outlet of each type and current rating		P
	During the test: no sustained arcing occur		P
	After the test the specimens do not show:		
	- wear impairing their further use;		P
	- deterioration of enclosures, insulating lining or barriers;		P
	- damage to the entry holes for the pins, that might impair proper working;		P
	- loosening of electrical or mechanical connections;		P
	- seepage of sealing compound		P
	Shuttered socket-outlets: gauges of figure 9 and 10 applied to the entry holes corresponding to live contacts do not touch live parts when they remain under the relevant forces	See appended table 21	P
	Temperature-rise test (requirements of clause 19)	See appended table 21	P
	Electric strength (sub-clause 17.2)	See appended table 21	P
	Pins which are not solid: test according to 14.2		P

22	FORCE NECESSARY TO WITHDRAW THE PLUG		P
	Construction of accessory does allow the easy insertion and withdrawal of the plug, and prevent the plug from working out of the socket-outlet in normal use		P
22.1	Verification of the maximum withdrawal force	See appended table 22	P
22.2	Verification of the minimum withdrawal force	See appended table 22	P

23	FLEXIBLE CABLES AND THEIR CONNECTIONS		N/A
23.1	Rewirable plugs and rewirable portable socket-outlets are provided with a cord anchorage		N/A
	Sheath of flexible cable is clamped within the cord anchorage		N/A
	In non-rewirable plugs and non-rewirable portable socket-outlets the cable is maintained in position and the terminations are relieved from strain and twisting		N/A
	Sheath of flexible cable is maintained inside the accessory		N/A
23.2	Pull and torque test		N/A
	Non-rewirable accessories:		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	After the test: displacement ≤ 2 mm	See appended table 23.2	N/A
	No break in the electrical connections		N/A
	Rewirable accessories:		N/A
	After the test: displacement ≤ 2 mm	See appended table 23.2	N/A
	End of conductors not have moved noticeably in the terminals		N/A
	Rewirable accessories having rated current up to and including 16 A:		N/A
	Suitable for fitting with the appropriate cable as shown in table 19		N/A
	Type of flexible cable; number of conductors and nominal cross-sectional area (mm ²)..... :		—
23.3	Non-rewirable plugs and non-rewirable portable socket-outlets are provided with a flexible cable complying with IEC 60227 or IEC 60245		N/A
	Flexible cables have the same number of conductors as there are poles in the plug or socket-outlet		N/A
	Conductor connected to the earthing contact is identified by the colour combination green/yellow		N/A
23.4	Non-rewirable plugs and non-rewirable portable socket-outlets: designed that the flexible cable is protected against excessive bending		N/A
	Guards of insulating material and fixed in reliable manner		N/A
	Flexing test (10.000 flexings)		N/A
	During the test: no interruption of the test current and no short-circuit between conductors	See appended table 23.4	N/A
	After the test: guard no separated from the body, insulation shows no sign of abrasion or wear, broken strands become no accessible	See appended table 23.4	N/A

24	MECHANICAL STRENGTH		P
	Accessories, surface mounting boxes, screwed glands and shrouds have adequate mechanical strength		P
24.1	Fixed socket-outlets, portable multiple socket-outlets and surface-type mounting boxes: hammer test described in IEC 60068-2-75 (test EHA), equivalent mass of 250 g	See appended table 24.1	P
	After the test: no damage, live parts no become accessible		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
24.2	Portable single socket-outlets and plugs: subjected to test Ec: Rough handling shocks, primarily for equipment-type specimens, procedure 2 of IEC 60068-2-31 (tumbling barrel); number of falls.....:		N/A
	After the test:		
	- no part become detached or loosened;		N/A
	- pins no become so deformed that the plug cannot be introduced into a socket-outlet and also fails to comply with the requirements of 9.1 and 10.3;		N/A
	- pins no turn when a torque of 0,4 Nm is applied for 1 min in each direction		N/A
	The shutters of socket-outlets tested again according to Clause 21, from paragraph 19 up to paragraph 24 (only the tests of shutters)		N/A
24.3	Main parts of surface-type socket-outlets: first fixed to a cylinder of rigid steel sheet and then fixed to a flat steel sheet		N/A
	During and after the tests: no damage		N/A
24.4	Portable single socket-outlets, multiple socket-outlets and plugs (elastomeric or thermoplastic material): impact test, weight (1000 ± 2) g, height 100 mm (apparatus shown in fig. 27)		N/A
	Specimens placed in a freezer at (-15 °C ± 2) °C for at least 16 h. After the test: no damage		N/A
24.5	Portable single socket-outlets and plugs (elastomeric or thermoplastic material): compression test, 300 N for 1 min, position a) and b) (apparatus shown in fig. 8)		N/A
	After the test: no damage		N/A
24.6	Screwed glands of accessories having IP>20: torque test (1 min)		N/A
	- diameter of test rod (mm)		—
	- type of material (metal / moulded)		—
	- torque (Nm)		—
	After the test: no damage of glands and enclosures of the specimens		N/A
24.7	Plug pins provided with insulating sleeves: 20000 movements, 4 N (apparatus shown in fig. 28)		N/A
	After the test: no damage of pins, insulating sleeve not have punctured or rucked up		N/A
24.8	Shuttered socket-outlets: mechanical test carried out on specimens submitted to the normal operation test according to clause 21		P
	Force (40 N / 75 N) applied for 1 min against the shutter of an entry hole by means of one pin (N) :	40	—
	Pin did not come in contact with live parts		P
	After the test: no damage		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
24.9	Mechanical test for multiple portable socket-outlet: 8 falls on concrete floor with the specimens arranged as shown in figure 29		N/A
	Rewirable multiple socket-outlets: flexible cable of the smallest cross-sectional area specified in table 3		—
	After the test: no damage, no part have become detached or loosened		N/A
	Accessories having IP>X0 submitted again to the tests as specified in 16.2		N/A
	The shutters of multiple socket-outlets tested again according to Clause 21, from paragraph 19 up to paragraph 24 (only the tests of shutters)		N/A
24.10	Plugs: pull test to verify the fixation of pins in the body of the plug (new specimens)		N/A
	Maximum withdrawal force (table 16) applied for 1 min on each pin in turn, after the specimen has been placed at (70 ± 2) °C for 1 h (N)		—
	After the test: displacement of pins in the body of the plug ≤ 1 mm (mm)		N/A
24.11	Barriers of portable socket-outlets having means for suspension on a mounting surface:		N/A
	Force applied for 10 s against the barrier by means of a cylindrical steel rod (1,5 times the maximum plug withdrawal force in 22.1, table 16) (N)		—
	Rod did not pierce the barrier		N/A
24.12	Portable socket-outlets having means for suspension on a mounting surface (pull test):		N/A
	Pull applied to the supply flexible cable for 10 s (force prescribed in 23.2 for checking the flexible cable anchorage) (N)		—
	During the test: no break of the means for suspension on a mounting surface		N/A
24.13	Portable socket-outlets having means for suspension on a mounting surface (pull test):		N/A
	Pull applied to the engagement face of the socket-outlet for 10 s (maximum withdrawal force specified, for the corresponding plug, in table 16) (N)		—
	During the test: no break of the means for suspension on a mounting surface		N/A
24.14	Forces necessary to retain or remove covers, cover-plates or parts of them (accessibility with the test finger to live parts)		N/A
24.14.1	Verification of the retention of covers or cover-plates (fixed socket-outlets)		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	Force (40 N / 80 N) applied for 1 min perpendicular to the mounting surface (N) :		—
	Covers or cover-plates did not come off		N/A
	Test repeated on new specimens with a sheet of hard material, (1 ± 0,1) mm thick, fitted around the supporting frame (fig. 31): covers or cover-plates did not come off		N/A
	After the test: no damage		N/A
24.14.2	Verification of the removal of covers or cover-plates (fixed socket-outlets)		N/A
	Force not exceeding 120 N applied 10 times perpendicular to the mounting / supporting surface: covers or cover-plates came off		N/A
	Test repeated on new specimens with a sheet of hard material, (1 ± 0,1) mm thick, fitted around the supporting frame (fig. 31): covers or cover-plates came off		N/A
	After the test: no damage		
24.14.3	Verification of the retention of covers or cover-plates (plugs and portable socket-outlets)		N/A
	Force 80 N applied for 1 min perpendicular to the mounting surface: covers, cover-plates or parts of them did not come off		N/A
	Test repeated with a force of 120 N:		N/A
	Rewirable plugs and rewirable portable socket-outlets: covers, cover-plates or parts of them came off but the specimen showed no damage		N/A
	Non-rewirable, non-moulded-on accessories: covers, cover-plates or parts of them came off but the accessories were permanently useless according to 14.1		N/A
24.15	Force necessary for covers or cover-plates to come off or not to come off (accessibility with the test finger to non-earthed metal parts separated from live parts by creepage distances and clearances according to table 23)		N/A
24.14.1	Verification of the non-removal of covers or cover-plates		N/A
	Force (10 N / 20 N) applied for 1 min in direction perpendicular to the mounting surface (N) :		—
	Covers or cover-plates did not come off		N/A
	Test repeated on new specimens with a sheet of hard material, 1 mm ± 0,1 mm thick, fitted around the supporting frame (fig. 31): covers or cover-plates did not come off		N/A
	After the test: no damage		N/A
24.14.2	Verification of the removal of covers or cover-plates		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict
	Force not exceeding 120 N applied 10 times in direction perpendicular to the mounting / supporting surface: covers or cover-plates came off		N/A
	Test repeated on new specimens with a sheet of hard material, 1 mm ± 0,1 mm thick, fitted around the supporting frame (fig. 31): covers or cover-plates came off		N/A
	After the test: no damage		
24.16	Force necessary for covers or cover-plates to come off or not to come off (accessibility to insulating parts, earthed metal parts, live parts of SELV ≤ 25 V a.c. or metal parts separated from live parts by creepage distances twice those according to table 23)		P
24.14.1	Verification of the non-removal of covers or cover-plates		
	Force 10 N applied for 1 min in direction perpendicular to the mounting surface: covers or cover-plates did not come off		P
	Test repeated on new specimens with a sheet of hard material, 1 mm ± 0,1 mm thick, fitted around the supporting frame (fig. 31): covers or cover-plates did not come off		P
	After the test: no damage		P
24.14.2	Verification of the removal of covers or cover-plates		P
	Force not exceeding 120 N applied 10 times in direction perpendicular to the mounting / supporting surface: covers or cover-plates came off		P
	Test repeated on new specimens with a sheet of hard material, 1 mm ± 0,1 mm thick, fitted around the supporting frame (fig. 31): covers or cover-plates came off		P
	After the test: no damage		P
24.17	Test with gauge of figure 7 applied according to figure 9 for verification of the outline of covers or cover-plates: distances between face C of gauge and outline of side under test, not decrease	not complying	—
24.18	Test with gauge according to figure 5 applied as shown in figure 11 (1 N): gauge not enter more than 1mm	complying	—
24.19	Shroud of portable socket-outlets: compression test (20 ± 2) N at (25 ± 5) °C by means of the apparatus shown in figure 38		N/A
	After 1 min and while the shrouds are still under pressure the dimensions did comply with the appropriate standard sheet		N/A
	Test repeated with the specimen rotated 90 °		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

25	RESISTANCE TO HEAT		P
25.1	Specimens kept for 1 h in a heating cabinet at (100 ± 2) °C for 1 h		P
	During the test: no change impairing their further use and sealing compound, if any, not flow		P
	After the test:		
	- no access to live parts with probe B of IEC 61032 applied with a force not exceeding 5 N		P
	- markings still legible		P
25.2	Parts of insulating material necessary to retain current-carrying parts and parts of the earthing circuit in position, as well as parts of the front surface zone, 2 mm wide, surrounding the phase and neutral pin entry holes: ball-pressure test at (125 ± 2) °C for 1 h	See appended table 25.2	P
25.3	Parts of insulating material not necessary to retain current-carrying parts and parts of the earthing circuit in position, even though in contact with them: ball-pressure test (1 h)	See appended table 25.3	P
25.4	Portable accessories: compression test (20 N) at (80 ± 2) °C for 1 h by means of the apparatus shown in figure 38		N/A
	After the test: no damage		

26	SCREWS, CURRENT-CARRYING PARTS AND CONNECTIONS		P
26.1	Connections withstand mechanical stresses		P
	Thread-forming or thread-cutting screws used only if supplied together with the piece in which they are intended to be inserted		N/A
	Thread-cutting screws intended to be used during installation: captive		N/A
	Screws or nuts which transmit contact pressure made of metal and in engagement with a metal thread		N/A
	Threaded part torque test	See appended table 26.1	N/A
26.2	Screws in engagement with a thread of insulating material: correct introduction into the screw hole or nut ensured		N/A
26.3	Contact pressure: not transmitted through insulating material other than ceramic, pure mica or other material no less suitable unless there is sufficient resiliency in metallic parts		P
	Connections made by insulation piercing of tinsel cord reliable		N/A
26.4	Screws and rivets locked against loosening and/or turning		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

26.5	Current-carrying parts (including earthing terminals) have mechanical strength, electrical conductivity and resistance to corrosion adequate:		P
	- copper;		N/A
	- alloy with at least 58 % copper for parts made from cold-rolled sheet or with at least 50 % copper for other parts;		P
	- stainless steel with at least 13 % chromium and not more than 0,09 % carbon		N/A
	- steel with electroplated coating of zinc (ISO 2081): service condition ISO no. (1/2/3); IP (X0/X4/X5); thickness (µm)		N/A
	- steel with electroplated coating of nickel and chromium (ISO 1456): service condition ISO no. (2/3/4); IP (X0/X4/X5); thickness (µm)		N/A
	- steel with electroplated coating of tin (ISO 2093): service condition ISO no. (2/3/4); IP (X0/X4/X5); thickness (µm)		N/A
	Current-carrying parts subjected to mechanical wear: not of steel with electroplated coating		P
	Metals having a great difference of electrochemical potential: not used in contact with each other		P
26.6	Contacts subjected to a sliding action are of metal resistant to corrosion		P
26.7	Thread-forming screws and thread-cutting screws are not used for the connection of current-carrying parts		N/A
	Thread-forming screws and thread-cutting screws used to provide earthing connection: it is not necessary to disturb the connection and at least two screws are used for each connection		N/A

27	CREEPAGE DISTANCES, CLEARANCES AND DISTANCES THROUGH SEALING COMPOUND		P
27.1	Creepage distances, clearances and distances through sealing compound are not less than the values shown in table 23	See appended table 27.1	P
27.2	Insulating sealing compound does not protrude above the edge of the cavity in which it is contained		P
27.3	Surface-type socket-outlets do not have bare current-carrying strips at the back		N/A

28	RESISTANCE OF INSULATING MATERIAL TO ABNORMAL HEAT, TO FIRE AND TO TRACKING		P
28.1	Resistance to abnormal heat and to fire		P

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

28.1.1	Glow-wire test according to IEC 60695-2-10 and IEC 60695-2-11	See appended table 28.1.1	P
28.1.2	Plugs with pins provided with insulating sleeves:		N/A
	Test temperature maintained for 3 h by means of the apparatus shown in figure 40 at (120 ± 5) °C / (180 ± 5) °C		—
	Impact test according to sub-clause 30.4 (mass 100 g, height 100 mm, 4 impacts): no cracks of the insulating sleeves		
28.2	Resistance to tracking		N/A
	Parts of insulating material retaining live parts in position of accessories having IP>X0: of material resistant to tracking		
	Tracking test at 175 V with solution A of IEC 60112	See appended table 28.2	

29	RESISTANCE TO RUSTING		P
	Ferrous parts protected against rusting		P
	Test made after having removed all grease using a suitable degreasing agent: 10 min 10 % solution of ammonium chloride, 10 min in a box with air saturated with moisture and 10 min at (100 ± 5) °C:		P
	No signs of rust		P

30	ADDITIONAL TESTS ON PINS PROVIDED WITH INSULATING SLEEVES		N/A
30.1	Pressure test at high temperature		N/A
	Apparatus shown in figure 41, with the test specimen in position, maintained for 2 h at (200 ± 5) °C. Force applied through the blade: 2,5 N		N/A
	Thickness of the insulation measured: before the test (mm); after the test (mm)		—
	Thickness remaining at the point of impression is not reduced by more than 50 % of its original value measured at the start of the test: percentage value (%)		N/A
30.2	Static damp heat test		N/A
	Set of 3 specimens submitted to two damp heat cycles in accordance with IEC 60068-2-30		N/A
	After the test:		
	- insulation resistance and electric strength test (clause 17)		N/A
	- abrasion test (sub-clause 24.7)		N/A
30.3	Test at low temperature		N/A

IEC 60884-1			
Clause	Requirement + Test	Result - Remark	Verdict

	Set of 3 specimens maintained at (-15 °C ± 2) °C for 24 h		N/A
	After the test:		
	- insulation resistance and electric strength test (clause 17)		N/A
	- abrasion test (sub-clause 24.7)		N/A
30.4	Impact test at low temperature		N/A
	Specimens maintained at (-15 °C ± 2) °C for 24 h subjected to 4 impacts (mass 100 g, height 100 mm) by means of the apparatus shown in figure 42 rotating the specimen through 90 ° between impacts		N/A
	After the test: no crack of the insulating sleeves		N/A

12.2.5	TABLE: test with apparatus shown in figure 11 (screw-type terminals)			N/A	
	rated current (A)	:		—	
	type of conductors	:		—	
	smallest/largest cross-sectional area per table 3 (mm ²)	:		—	
	number of conductors	:		—	
	nominal diameter of thread (mm); torque per table 6 (Nm)	:		—	
	Cross-sectional area (mm ²)	Diameter of bushing hole per table 9 (mm)	Height H per table 9 (mm)	Mass (kg)	Remarks
supplementary information:					

12.2.6	TABLE: pull test (screw-type terminals)			N/A	
	rated current (A)	:		—	
	smallest/largest cross-sectional area per table 3 (mm ²)	:		—	
	nominal diameter of thread (mm); torque 2/3 per table 6 (Nm)	:		—	
	Cross-sectional area (mm ²)	Number of conductors	Type of conductors (rigid solid / rigid stranded / flexible)	Pull per table 4 applied for 1 min (N)	Remarks
supplementary information:					

12.2.7	TABLE: tightening test (screw-type terminals)			N/A	
	rated current (A)	:		—	
	nominal diameter of thread (mm); torque 2/3 per table 6 (Nm)	:		—	
	Largest cross-sectional area per table 3 (mm ²)	Permissible number of conductors ⁽¹⁾	Type of conductors (rigid solid / rigid stranded / flexible)	Number of wires and nominal diameter of wires per table 5	Remarks
supplementary information:					
⁽¹⁾ terminals intended for looping-in 2 or 3 conductors					

12.3.10	TABLE: mechanical strength test (screwless-type terminals)				P	
	rated current (A)	:	16		—	
	largest/smallest cross-sectional area per table 7 (mm ²)	:	2,5 / 1,5		—	
	Number of connection (after that conductor subjected to a pull of 30 N for 1 min) / disconnection	Type of conductor (solid / rigid stranded / flexible)	Cross-sectional area (mm ²)	Remarks		
	5	SOLID	2,5	P		
	5	SOLID	1,5	P		
	5	STRANDED	2,5	P		
	5	STRANDED	1,5	P		
	5	FLEXIBLE	2,5	P		
	5	FLEXIBLE	1,5	P		
	TABLE: test with apparatus shown in figure 11				P	
	Cross-sectional area (mm ²)	Type of conductor (solid / rigid stranded / flexible)	Diameter of bushing hole per table 9 (mm)	Height H per table 9 (mm)	Mass (kg)	Remarks
	2,5	SOLID	9,5	280	0,7	P
	1,5	SOLID	6,5	260	0,4	P
	2,5	STRANDED	9,5	280	0,7	P
	1,5	STRANDED	6,5	260	0,4	P
	2,5	FLEXIBLE	9,5	280	0,7	P
	1,5	FLEXIBLE	6,5	260	0,4	P
supplementary information:18-1149; 18-1150; 18-1151;						

12.3.11	TABLE: electrical and thermal strength test				P
Test a)	Test carried out for 1 h connecting rigid solid conductors:				P
	test current per table 10 (A)	:	22		—
	nominal cross-sectional area (mm ²)	:	2,5		—
	Screwless terminal number	Voltage drop (mV)		Required voltage drop (mV)	
	1	9,5		≤15	
	2	8,2		≤15	
	3	8,9		≤15	
	4	8,3		≤15	
	5	10,2		≤15	
Test b)	Temperature cycles test carried out on terminals subjected to Test a):				P
	test current per table 10 (A)	:	22		—
	nominal cross-sectional area (mm ²)	:	2,5		—
	allowed voltage drop (mV)	:	≤ 22,5 mV or 2 times 24 th cycle value (mV)		—

Screwless terminal number	1	2	3	4	5	Remarks
voltage drop after 24 th cycle	9,2	7,9	8,5	8,1	9,9	P
voltage drop after 48 th cycle	9,8	8,1	8,6	8,2	9,9	P
voltage drop after 72 nd cycle	9,3	8,0	8,5	8,1	9,5	P
voltage drop after 96 th cycle	9,1	8,0	8,6	8,2	9,4	P
voltage drop after 120 th cycle	9,0	7,9	8,5	8,1	9,3	P
voltage drop after 144 th cycle	11,5	9,4	8,6	8,2	10,5	P
voltage drop after 168 th cycle	11,1	9,2	8,5	8,2	10,0	P
voltage drop after 192 nd cycle	11,0	9,2	8,5	8,2	10,0	P
12.3.10	TABLE: mechanical strength test (screwless-type terminals)					P
	rated current (A) : 16					—
	largest/smallest cross-sectional area per table 7 (mm ²) : 2,5					—
Number of connection (after that conductor subjected to a pull of 30 N for 1 min) / disconnection	Type of conductor (solid / rigid stranded / flexible)		Cross-sectional area (mm ²)		Remarks	
5	SOLID		2,5		P	
5	SOLID		1,5		P	
5	STRANDED		2,5		P	
5	STRANDED		1,5		P	
5	FLEXIBLE		2,5		P	
5	FLEXIBLE		1,5		P	
	TABLE: test with apparatus shown in figure 11					N/A
Cross-sectional area (mm ²)	Type of conductor (solid / rigid stranded / flexible)	Diameter of bushing hole per table 9 (mm)	Height H per table 9 (mm)	Mass (kg)	Remarks	
2,5	SOLID	9,5	280	0,7	P	
1,5	SOLID	6,5	260	0,4	P	
2,5	STRANDED	9,5	280	0,7	P	
1,5	STRANDED	6,5	260	0,4	P	
2,5	FLEXIBLE	9,5	280	0,7	P	
1,5	FLEXIBLE	6,5	260	0,4	P	
supplementary information: TEST ON 18-1152; 18-1153; 18-1154;						

12.3.12	TABLE: deflection test (principle of test apparatus shown in figure 12a)					P
	Test carried out connecting rigid solid copper conductors:					P
	test current (A) (equal rated current) : 16					—
	required voltage drop (mV) : ≤ 25 mV					—
Type of conductor	Smallest		Largest		Remarks	

cross-sectional area per table 11 (mm ²)	1,5			2,5			P
force per table 12 (N)	0,5			1,0			P
screwless terminal number	1	2	3	1	2	3	
starting point (X = deflection original point)	X	X+10°	X+20°	X	X+10°	X+20°	
voltage drop 1st deflection (mV)	9,8	10,7	9,2	11,2	9,2	10,8	P
voltage drop 2nd deflection (mV)	9,8	10,0	9,4	11,2	9,3	9,7	P
voltage drop 3rd deflection (mV)	11,5	10,2	9,7	13,4	9,9	9,4	P
voltage drop 4th deflection (mV)	13,2	13,3	10,9	14,8	12,4	11,9	P
voltage drop 5th deflection (mV)	14,6	15,1	13,9	14,9	12,8	13,5	P
voltage drop 6th deflection (mV)	7,3	10,4	10,7	10,9	10,2	9,3	P
voltage drop 7th deflection (mV)	8,1	9,5	9,4	9,4	10,2	8,8	P
voltage drop 8th deflection (mV)	9,9	12,6	10,7	9,4	11,1	9,6	P
voltage drop 9th deflection (mV)	10,5	9,7	10,9	10,8	10,1	9,5	P
voltage drop 10th deflection (mV)	9,6	10,7	9,6	16,9	11,3	10,3	P
voltage drop 11th deflection (mV)	8,8	10,3	9,2	10,6	11,5	10,6	P
voltage drop 12th deflection (mV)	8,6	8,8	8,8	9,9	12,3	9,8	P
supplementary information: TEST ON 18-1152; 18-1153; 18-1154;							

17.1	TABLE: insulation resistance			P
Item per 17.1	test voltage applied between:	measured (MΩ)	required (MΩ)	
18-1149	Between all poles connected together and the body	>1000	> 5	
18-1149	Between each pole in turn and all other		> 5	
18-1150	Between all poles connected together and the body		> 5	
18-1150	Between each pole in turn and all other		> 5	
18-1151	Between all poles connected together and the body		> 5	
18-1151	Between each pole in turn and all other		> 5	
supplementary information:				

17.2	TABLE: electric strength			P
	rated voltage (V)	250		—
item per 17.1	test voltage applied between:	test voltage (V)	flashover / breakdown (Yes/No)	
18-1149	Between all poles connected together and the body	2000	No	
18-1149	Between each pole in turn and all other	2000	No	
18-1150	Between all poles connected together and the body	2000	No	
18-1150	Between each pole in turn and all other	2000	No	

18-1151	Between all poles connected together and the body	2000	No
18-1151	Between each pole in turn and all other	2000	No

supplementary information:

19	TABLE: temperature rise test			P
	rated current of accessory (A)	16		—
	type of accessory (non-rewirable / rewirable)	rewirable		—
	nominal cross-sectional area per table 15 (mm ²) (rewirable accessories) / type of conductor	2,5		—
	type of conductors (rigid solid / rigid stranded / flexible) (rewirable accessories)	Rigid solid		—
	nominal diameter of thread (mm); torque 2/3 of that specified in 12.2.8 (Nm) (rewirable accessories) ...	N/A		—

specimen	type of flexible cable ⁽¹⁾	number of conductors and nominal cross-sectional area (mm ²) ⁽¹⁾	test circuit (L-L/L-N/L-E)	test current (table 20) for 1 h (A)	measured dT (K)	allowed dT (K)	temperature rise of external parts of insulating material (25.3)
18-1149	-	2,5	L-N	22	30,3	45	<5°K
18-1150	-	2,5	L-N	22	31,7	45	<5°K
18-1151	-	2,5	L-N	22	40,7	45	<5°K
18-1149	-	2,5	L-E	22	34,9	45	<5°K
18-1150	-	2,5	L-E	22	38,5	45	<5°K
18-1151	-	2,5	L-E	22	33,4	45	<5°K
18-1149	-	2,5	E	22	23,0	45	<5°K
18-1150	-	2,5	E	22	24,1	45	<5°K
18-1151	-	2,5	E	22	24,7	45	<5°K
18-1193	-	2,5	L-N	22	30,2	45	<5°K
18-1194	-	2,5	L-N	22	37,2	45	<5°K
18-1195	-	2,5	L-N	22	39,7	45	<5°K
18-1193	-	2,5	L-E	22	34,9	45	<5°K
18-1194	-	2,5	L-E	22	33,7	45	<5°K
18-1195	-	2,5	L-E	22	31,9	45	<5°K
18-1193	-	2,5	E	22	24,0	45	<5°K
18-1194	-	2,5	E	22	22,4	45	<5°K
18-1195	-	2,5	E	22	21,0	45	<5°K

supplementary information: see all temperature data on file "T_r_test.xlsx"

⁽¹⁾ Non-rewirable accessories

20	TABLE: breaking capacity								P
	rating of accessory (A/V)			16/250			—		
	type of accessory (non-rewirable / rewirable)			rewirable			—		
	type of flexible cable (non-rewirable accessories) :			N/A			—		
	number of conductors and nominal cross-sectional area (mm ²) (non-rewirable accessories) :			N/A			—		
	nominal cross-sectional area per table 15 (mm ²) (rewirable accessories) / type of conductor			2,5 RIGID			—		
	type of conductors (rigid solid / rigid stranded / flexible) (rewirable accessories)			RIGID			—		
	nominal diameter of thread (mm); torque 2/3 of that specified in 12.2.8 (Nm) (rewirable accessories) ... :			N/A			—		
	rate of operation (strokes per minute)			30			—		
specimen	test plug (for each type and current rating of socket-outlet)		test voltage (1,1 V _n) (V)	test current (1,25 I _n) cos φ 0,6 (A)	number of strokes (plugs only)	number of strokes, with shutters – with current ⁽¹⁾	number of strokes, without shutters – with current ⁽²⁾	remarks	
	pin dimensions (mm)	pin spacing (mm)							
18-1149	4,8	19,0	275	20	-	100	-	P	
18-1150	4,8	19,0	275	20	-	100	-	P	
18-1151	4,8	19,0	275	20	-	100	-	P	
supplementary information:									
⁽¹⁾ starting point 1 or 3 of Figure 43									
⁽²⁾ starting point 2 of Figure 43									

21	TABLE: normal operation								P
	rating of accessory (A/V)			16/250			—		
	type of accessory (non-rewirable / rewirable)			rewirable			—		
	type of flexible cable (non-rewirable accessories) :			N/A			—		
	number of conductors and nominal cross-sectional area (mm ²) (non-rewirable accessories) :			N/A			—		
	nominal cross-sectional area per table 15 (mm ²) (rewirable accessories) / type of conductor			2,5 RIGID			—		
	type of conductors (rigid solid / rigid stranded / flexible) (rewirable accessories)			RIGID			—		
	nominal diameter of thread (mm); torque 2/3 of that specified in 12.2.8 (Nm) (rewirable accessories) ... :			N/A			—		
	rate of operation (strokes per minute)			30			—		

specimen	test plug (for each type and current rating of socket-outlet)		test voltage (V _n) (V)	test current (table 20), cos φ 0,8 (A)	number of strokes (plugs only)	number of strokes, with shutters – with current ⁽¹⁾	number of strokes, without shutters – with current ⁽²⁾	number of strokes, with shutters – without current ⁽³⁾	
	pin dimensions (mm)	pin spacing (mm)							
18-1149	4,8	19,0	250	16	-	10000	-	-	P
18-1150	4,8	19,0	250	16	-	10000	-	-	P
18-1151	4,8	19,0	250	16	-	10000	-	-	P
TABLE: test for shuttered socket-outlets									
specimen	Gauge of figure 9, applied with a force of 20 N, for approximately 5 s, successively in three directions				Steel gauge of figure 10, applied with a force of 1 N for approximately 5 s, in three directions				
18-1149	P				P				P
18-1150	P				P				P
18-1151	P				P				P
19	TABLE: temperature rise test								
specimen	test circuit (L-L/L-N/L-E)	test current (table 20 for clause 21) for 1 h (A)		measured dT (K)	allowed dT (K)				
18-1149	L-N	16		23,9	<45	P			
18-1150	L-N	16		21,2	<45	P			
18-1151	L-N	16		21,8	<45	P			
18-1149	L-E	16		29,4	<45	P			
18-1150	L-E	16		31,6	<45	P			
18-1151	L-E	16		34,1	<45	P			
18-1149	E	16		18,1	<45	P			
18-1150	E	16		20,8	<45	P			
18-1151	E	16		19,6	<45	P			
17.2	TABLE: electric strength								
specimen	item per 17.1	test voltage applied between:			test voltage (V)	flashover / breakdown (Yes/No)			
18-1149	A	Between all poles connected together and the body			1500	No			
18-1149	B	Between each pole in turn and all other			1500	No			
18-1150	A	Between all poles connected together and the body			1500	No			
18-1150	B	Between each pole in turn and all other			1500	No			

18-1151	A	Between all poles connected together and the body	1500	No
18-1151	B	Between each pole in turn and all other	1500	No
supplementary information: ⁽¹⁾ starting point 1 or 3 of Figure 43 ⁽²⁾ starting point 2 of Figure 43 ⁽³⁾ starting point 1 or 2 of Figure 43				

22	TABLE: force necessary to withdraw the plug				P
	Rated current (A)		16		—
	Number of poles		2		—
22.1	Verification of the maximum withdrawal force				
specimen	socket-outlets (multi-pin gauge)		plugs with resilient earthing contact assemblies (single-pin gauge)		
	maximum withdrawal force (N)	the test plug did not remain in the socket-outlet (Y/N)	maximum withdrawal force (N)	the test pin gauge did not remain in the contact assembly	
18-1149	50	Y	-	-	P
18-1150	50	Y	-	-	P
18-1151	50	Y	-	-	P
22.2	Verification of the minimum withdrawal force				P
specimen	socket-outlets (single-pin gauge)		plugs with resilient earthing contact assemblies (single-pin gauge)		
	minimum withdrawal force (N)	the test pin gauge did not fall from each individual contact-assembly within 30 s (Y/N)	minimum withdrawal force (N)	the test pin gauge did not fall from each individual earthing contact-assembly within 30 s (Y/N)	
18-1149	2	Y	-	-	P
18-1150	2	Y	-	-	P
18-1151	2	Y	-	-	P
supplementary information:					

24.1	TABLE: impact test			P
part of enclosure tested per table 21 (A, B, C, D)		blows per part	height of fall (mm)	comments
A		5	80	P
B		4	80	P

supplementary information: test on 18-1149; 18-1150; 18-1151;

25.2	TABLE: ball pressure test of insulating materials	P
------	--	----------

	allowed impression diameter (mm)	≤ 2 mm	—
part under test		test temperature (°C)	impression diameter (mm)
BASE W0C0025_21 Polycarbonate RAL7011		125	1,1
Support contact W0C0010_13 PC RAL7035		125	1,0
Cover w0c0025_80 Polycarbonate		125	1,2

Shutter support W0C0026_13 Polycarbonate PC 10% FG	125	1,4	
supplementary information: test on 18-1149; 18-1150; 18-1151;			

25.3	TABLE: ball pressure test of insulating materials			P
	allowed impression diameter (mm)	≤ 2 mm	—	
part under test		test temperature (°C) ⁽¹⁾	impression diameter (mm)	

SHUTTER W0F0005_15 PBT 30% FG + PTFE	70	0,8		
supplementary information: test on 18-1149; 18-1150; 18-1151;				
⁽¹⁾ (70 ± 2) °C / (40 ± 2) °C + highest temperature rise determined during the test of clause 19				

27.1	TABLE: creepage distances, clearances and distances through sealing compound							P
	rated voltage (V)							—
item per table 23	creepage distance dcr, clearance cl and distance through sealing compound dtsc at/of:	required cl (mm)	cl (mm)	required dcr (mm)	dcr (mm)	required dtsc (mm)	dtsc (mm)	
1	Between live parts of different polarity	≥ 3	>4	≥ 3	>4	≥ 3	-	
2	Between live parts and	≥ 3	>8	≥ 3	>8	≥ 3	-	

28.1.1	TABLE: glow-wire test						P
part under test	material designation	test temperature (°C)	visible flame and sustained glowing (Y/N)	flame and glowing extinction time	ignition of the tissue paper (Y/N)		
Complete product	ALL	850	Y	10	N		

28.2	TABLE: resistance to tracking				N/A
	number of drops	50			—
part under test	material designation	test voltage (V)	flashover / breakdown (Yes/No)		

List of test equipment used:

Clause	Measurement / testing	Testing / measuring equipment / material used, (Equipment ID)	Description	Last Calibration date	Calibration due date
8	time	w8t0002-01	chrono	09/2016	09/2019
9	time	w8t0002-01	chrono	09/2016	09/2019
9	mass	w8m0042-01	mass 150N	09/2016	09/2019
10	gauge	w8d0009-03	finger	03/2018	03/2020
10	gauge	w8d0010-03	finger	03/2018	03/2020
10	time	w8t0002-01	chrono	09/2016	09/2019
10	gauge	w8d0011-03	acc. 20N	02/2018	02/2020
10	gauge	w8d0012-03	acc. 1N	02/2018	02/2020
10	mass	w8m0042-01	mass 150N	09/2016	09/2019
11	time	w8t0002-01	chrono	09/2016	09/2019
11	electric	w8e0001-06	multimeter	11/2018	11/2019
12	electric	w8e0003-02	generator	11/2018	11/2019
12	electric	w8e0011-04	multimeter	11/2018	11/2019
12	electric	w8e0004-02	generator	11/2018	11/2019
12	electric	w8e0002-10	datalogger	11/2018	11/2019
12	equipment	w8n0005-05	support	09/2016	09/2020
12	mass	w8m0016-01	0,7 Kg	12/2016	12/2019
12	mass	w8m0015-01	0,4 Kg	12/2016	12/2019
12	time	w8t0002-01	chrono	09/2016	09/2019
13	gauge	w8d0031-03	gauge	03/2018	03/2020
13	mass	w8m0012-01	5N	12/2016	12/2019
13	time	w8t0002-01	chrono	09/2016	09/2019
16	temperature	w8k0001-04	climatic C	10/2018	10/2019
17	electric	w8e0002-06	HV generator	11/2018	11/2019
17	electric	w8e0001-06	multimeter	11/2018	11/2019
17	time	w8t0002-01	chrono	09/2016	09/2019
19	electric	w8e0003-02	generator	11/2018	11/2019
19	electric	w8e0006-10	datalogger	11/2018	11/2019
19	gauge	w8d0146-03	plug	10/2018	09/2019
19	gauge	w8d0143-03	plug	09/2018	09/2019
19	gauge	w8d0145-03	plug	09/2018	09/2019
19	gauge	w8a0098-00	earth plug	05/2018	05/2019
20/21	electric	w8e0001-12	load	11/2018	11/2019
20/21	electric	w8e0005-12	load	11/2018	11/2019

20/21	gauge	w8d0146-03	plug	10/2018	09/2019
20/21	gauge	w8d0143-03	plug	10/2018	09/2019
20/21	gauge	w8d0145-03	plug	10/2018	09/2019
20/21	gauge	w8a0098-00	earth plug	06/2018	06/2019
20/21	electric	w8e0002-06	HV generator	11/2018	11/2019
20/21	electric	w8e0003-02	generator	11/2018	11/2019
20/21	electric	w8e0006-10	datalogger	11/2018	11/2019
22	mass	w8m0007-01	50N	12/2016	12/2019
22	mass	w8m0037-01	200g	05/2017	05/2020
24	equipment	w8n0004-05	support	09/2016	09/2020
24	mass	w8m0040-01	hammer 250g	09/2016	09/2019
25	temperature	w8k0003-04	climatic C	10/2018	10/2019
25	mass	w8n0002-02	Ball p. 20N	04/2018	04/2020
25	mass	w8n0004-02	Ball p. 20N	04/2018	04/2020
25	time	w8t0002-01	chrono	09/2016	09/2019
25	dimensional	w8d0001-07	OGP	05/2017	05/2019
28	electric	w8e0009-04	amperometer	11/2018	11/2019
28	equipment	w8k0002-05	glow wire	09/2016	09/2020
28	time	w8t0002-01	chrono	09/2016	09/2019
29	temperature	w8k0003-04	climatic C	10/2018	10/2019
29	temperature	w8k0001-04	climatic C	10/2018	10/2019
29	time	w8t0002-01	chrono	09/2016	09/2019
9	electric	w8e0004-04	48V	n.a.	n.a.
9	gauge	w8d0089-03	F: c1 / BE: c18	03/2016	03/2019
9	gauge	w8g0009-01	F: c2 / BE: c1	03/2016	03/2019
9	gauge	w8d0045-03	F: c3 / BE: c7	05/2018	05/2019
9	gauge	w8m0039_01_400	F: c4 / BE: c2	05/2017	05/2020
22	gauge	w8m0039_01_200	F: c4 / BE: c2	05/2017	05/2020
9	gauge	w8d0082-03	F: c5 / BE: c3	03/2016	03/2019
9	gauge	w8d0076-03	F: c6 / BE: c11	03/2016	03/2019
9	gauge	w8d0132-03	BE: C9a	03/2018	03/2020
9	gauge	w8d0133-03	BE: C9b	03/2018	03/2020
9	gauge	w8d0126-03	BE: C43	10/2018	10/2019

SGS Belgium NV
Division SGS CEBEC

Boulevard Internationalelaan, 55 Build D
B-1070 Brussel-Belgium
Cebec.info@sgs.com
www.cebex.sgs.com
T 0032 2 556 00 38 / F 0032 556 00 20