



application software



DALI broadcast 4-output module

Electrical/Mechanical characteristics: see product user manual

Product reference	Product designation	Application software ref	TP device Radio device (
TXA664D	DALI broadcast 4-output module	STXA664D 1.x Version	



Content

1 General	. 4
1.1 About this guide	
1.2 About the program	
1.2.1 ETS compatibility	. 4
1.2.2 Application descriptions	
1.3 software appearance	
2 General Description	
2.1 Installation of the device	. 5
2.1.1 Overview presentation	. 5
2.1.2 Description of the device	. 6
2.1.4 Connection	. 6
2.1.5 LED meaning	
2.2 Function modules of the application	. 8
2.2.1 DALI Protocol	. 8
2.2.2 Primary functions	. 9
2.2.3 Colour temperature	
2.2.4 Colour	
2.3 Behaviour of the device	
2.3.2 Behaviour on mains supply cut	
3 Programming by ETS	
3.1 Parameters	
3.1.1 Fixed parameters	
3.1.2 General	
3.1.3 Output functionalities	
3.1.3.1 Definition	14
3.1.3.2 Additional parameters	
3.1.3.3 Timer	17
3.1.3.4 Priority	18
3.1.3.5 Automatic control	
3.1.3.6 Scene	
3.1.4 DALI	
3.2 Communication objects	26
3.2.1 Communication objects Dimmer	
3.2.1.1 ON/OFF	
3.2.1.2 Dimming	20
3.2.1.4 Status indication	
3.2.1.5 Timer	
3.2.1.6 Scene	
3.2.1.7 Priority	
3.2.2 Communication objects Colour temperature	32
3.2.2.1 ON/OFF	
3.2.2.2 Dimming	
3.2.2.3 Colour temperature	
3.2.2.4 Automatic control	
3.2.2.5 Status indication	
3.2.2.6 Timer	
3.2.2.7 Scene	
3.2.2.8 Priority	30
3.2.3.1 ON/OFF	
3.2.3.2 Dimming	
3.2.3.3 Colour	
3.2.3.4 Automatic control	
3.2.3.5 Status indication.	
3.2.3.6 Timer	
3.2.3.7 Scene	
3.2.3.8 Priority	50
4 Programming by Easy Tool	52
4.1 Product overview	52



4.2 Product functionalities	56
4.2.1 ON/OFF	
4.2.2 Relative or absolute dimming (Brightness value)	57
4.2.3 Dimmer and switch principle	59
4.2.4 Timer	
4.2.5 Priority	62
4.2.6 Automatic control	64
4.2.7 Scene	
4.2.8 Colour	
4.2.9 Colour temperature	70
Appendix	71
5.1 Specifications	71
5.2 Characteristics	71



1 General

1.1 About this guide

The purpose of this manual is to describe the operation and configuration of the KNX-devices using the ETS program.

It consists of 4 parts:

- General information.
- The parameters and KNX objects available.
- The Easy tool configurations are available.
- Technical characteristics.

1.2 About the program

1.2.1 ETS compatibility

The application programs are compatible with ETS5. They can be downloaded from our website under the order number.

ETS Version	File extension of compatible files
ETS5 (V5.6.0 or higher)	*.knxprod

1.2.2 Application descriptions

Application	Product reference
STXA664D	TXA664D

1.3 software appearance

This product can also be configured using the TXA100 configuration tool. It is composed of a TJA665 configuration server.

Compatible software version TXA100: V 1.4.8.0 or higher


It is essential to update the configuration server software version. (Please refer to the TXA100 user manual).



2 General Description

2.1 Installation of the device


2.1.1 Overview presentation





2.1.2 Description of the device

- ① Connection to the power supply (N, L)
- 2 Connections to the DALI ballasts (da+, da-)
- 3 Auto/Manu switch (
- 4 Status LED
- (5) Local command buttons
- 6 Illuminated physical addressing button
- 7 Label holder
- (8) KNX bus connection terminals (-, +)
- (9) Overload fault LED



2.1.3 Physical addressing


In order to perform the physical addressing or to check whether or not the bus is connected, press the lighted push button (6) on the right-hand side above the identification plates on the front of the device.

Light on = bus connected and ready for physical addressing.

Programming mode is activated, until the physical address is transferred from ETS. Pressing the button again, exits programming mode. Physical addressing can be carried out in automatic or manual mode.


2.1.4 Connection

- On 1 channel





- On 2 channels



2.1.5 LED meaning

LED	LED/Operation status	
		output active
Cx		output inactive
red		short-circuit detected, flashes every 0.5 s
		no ballast or lamp fault, flashes every 0.5 s for 5 s




2.2 Function modules of the application

2.2.1 DALI Protocol

DALI (Digital Addressable Lighting Interface) is a standardised international communication and interoperability protocol for lighting management system components. This protocol exists to ensure that lighting manufacturers and fitters have a perfect compatibility between the materials that are fitted.

It is a lighting systems communication protocol that just as well suited to the management needs of an installation with several lights as it is to controlling the lighting in an entire building or an outdoor lighting installation. DALI lighting solutions can be integrated, via walkways, into the technical management systems of a building (KNX, BACnet, TCP/IP, etc.) or other systems.

Operating principle



Note: The elements that distinguish DALI 2 from the previous DALI version are its interoperability (the assurance of compatibility with all DALI equipment) and certification (guarantee of interoperability with a product from a different manufacturer).

Note: This product is certified DALI2. In the event of a malfunction, please check that the controlled ballasts are DALI2 certified.



2.2.2 Primary functions

The applications allow individual configuration of the device outputs.

The most important functions are:

■ ON/OFF

An output can be switched on or off using the ON/OFF function. The command can come from switches, buttons or other control inputs.

■ Relative or absolute dimming (Brightness value)

With relative dimming, the brightness value is raised or lowered with respect to the current brightness value. This is achieved, for example, by a long press on a sensor button. With absolute dimming, the brightness value to be achieved is set on the dimmer as a % value.

■ Timer

The Timer function can switch a lighting circuit on or off for a configurable period. The output can be switched to a desired brightness level for a specified period. The timer may be interrupted before expiry of the delay time. A programmable Cut-OFF pre-warning announces the end of the delay time by halving the present brightness value of the output.

■ Priority

The Priority function is used to force the output into a defined state. The Priority function is controlled with a 2-bit command.

Only a Priority OFF command authorizes the output for control.

Application: Keeping lighting on for security reasons.

Automatic control

The Automation functionality allows commanding an output at the same time as the ON/OFF functionality or lighting value. The two functions have the same level of priority. The last command received will act on the status of the output.

An additional command object is used to activate or deactivate the Automatic control.

■ Scene

The Scene function is used to switch groups of outputs into a configurable predefined state.

A scene is activated by receipt of a 1-byte command.

Each output can be included in 64 different scenes.

■ Manual mode


Manual mode allows the device to be disconnected from the bus. In this mode, each output can be priority controlled locally.

Status indication

The Status function sends the status of each output channel on the KNX bus.




Communication objects



2.2.3 Colour temperature

The product supports the control of the "Colour Control" DALI equipment (DALI Device Type 8) in the specific character "Tunable White (TW)". Using appropriate DALI equipment and lighting sources enables the colour temperature of a lamp to be controlled. The product controls the colour temperature via full dimming and stages. The colour temperature setting is largely independent of the luminosity setting of the lamps used.

Communication objects






2.2.4 Colour

The product supports the control of the "Colour Control" DALI equipment (DALI Device Type 8). Using appropriate DALI equipment and lighting sources enables the colour of a RGB(W) LED lamp to be controlled. The product controls each colour via a switch, full dimming and stages. The colour setting is largely independent of the luminosity setting of the lamps used.

Communication objects





2.3 Behaviour of the device

2.3.1 Behaviour after bus power cut

The table below defines the behaviour of the product.

Conditions: 230V mains supply for the product and DALI ballasts is available.

Channel function	During KNX-bus power cut	On return from theKNX-bus
Dimmer	Dimming: 100%	Dimming: Value before bus power cut
Colour temperature	Dimming: 100% Colour temperature: 5000K	Dimming: Value before bus power cut Colour temperature: Value before bus power cut
Colour	Dimming: 100% RGBW values: 100%	Dimming: Value before bus power cut RGBW values: Value before bus power cut

2.3.2 Behaviour on mains supply cut

The table below defines the behaviour of the product.

Conditions: 230V mains supply for DALI ballasts is available.

KNX mains supply is available.

Channel function	During the 230V mains supply cut	On return from the 230V mains supply
Dimmer	Dimming: 100%	Dimming: Value before bus power cut
Colour temperature	Dimming: 100% Colour temperature: 5000K	Dimming: Value before bus power cut Colour temperature: Value before bus power cut
Colour	Dimming: 100% RGBW values: 100%	Dimming: Value before bus power cut RGBW values: Value before bus power cut



3 Programming by ETS

The function of the different devices only differs in the number of outputs. For this reason, only one device or one output will ever be described.

3.1 Parameters

3.1.1 Fixed parameters

The fixed parameters define the operating mode of the output relays.

Parameter	Description	Value
Status after ETS download	The output status remains unchanged after ETS download.	Maintain status
	Note: During ETS-parameters download, the outputs remain unchanged.	
Parameters overwrite at next download (scenes)	The parameter values stored in the device will be overwritten with the ETS configured values at the next download.	Active
Status after priority	At the end of the priority, the output is: Switched back to the status before priority was activated.	Status before priority
Status after bus power cut	The output status remains unchanged during at bus return.	Maintain status
	Note: The device will reboot on bus return. The priority functions that were present before the bus power cut, are no longer active (Priority).	
Status at supply return	The output status remains unchanged when the power is turned back on. Note: The priority functions that were present before the bus power cut, are no longer active (Priority).	Maintain status

3.1.2 General

Outputs naming


Parameter	Description	Value
Output x name	This free text field is used to assign a name to the output in question. The group objects Name field will automatically be updated after input.	Output x*

x = 1 to 4




3.1.3 Output functionalities

This parameter window is used to set the device outputs. These parameters are available individually for each output.




Parameter	Description	Value
Channel function	This configuration window is used to set the operating mode of	Dimmer*
	the output channel.	Colour
		Colour temperature

3.1.3.1 Definition





Dimmer and switch principle:




- 1 Switch ON speed (soft ON)
- 2 Switch OFF speed (soft OFF)

Parameter	Description	Value
Last known brightness value at switch On	On receipt of an ON command on the ON/OFF communication object, the output is set to the following value:	
	100%	Not active
	To the last brightness value	Active*
Switch ON speed (soft ON)	This parameter defines the switch ON speed for attaining the brightness value after input of an ON command.	0 *1h45m00s
Switch OFF speed (soft OFF)	This parameter defines the switch OFF speed for attaining brightness value 0% after input of an OFF command.	0 *1h45m00s
Minimum dimming value (1 - 50%)	This parameter specifies a minimum brightness value for the dimming.	1*50
Maximum dimming value (51 - 100%)	This parameter specifies a maximum brightness value for the dimming.	51 100 *

3.1.3.2 Additional parameters

Additional parameters are available depending on the channel type selected.

■ Colour temperature





Parameter	Description	Value
•	This parameter defines the minimum colour temperature level for dimming.	1000 2000 *5000K
•	This parameter defines the maximum colour temperature level for dimming.	5010 6000 *10000K

Communication objects:

4, 42, 80, 118 – Output x – Colour temperature in K (2-byte-7.600 DPT_Absolute_Colour_Temperature) 5, 43, 81, 119 – Output x – Colour temperature in % (1-byte-5.001 DPT_Scaling) 12, 50, 88, 126 – Output x – Status indication colour temperature in % (1-byte-5.001 DPT_Scaling) 13, 51, 89, 127 – Output x – Status indication colour temperature in K (2-byte-7.600 DPT_Absolute_Colour_Temperature)

■ Colour



Parameter	Description	Value
Colour components	This parameter defines the colour components used for the	Red/Green/Blue*
	corresponding output channel.	Red/Green/Blue/White

Parameter	Description	Value
Colour objects	This parameter defines the size of items used to control the colours. All of the colours are controlled using:	
	- Several items	Simple
	- One unique item	Combined*
	- Several items and a single item	Both

Communication objects:

```
7, 45, 83, 121 – Output x – RGBW values (6-byte-251.600 DPT_Colour_RGBW) 8, 46, 84, 122 – Output x – RGB values (3-byte-232.600 DPT_Colour_RGB) 9, 47, 85, 123 – Output x – Red value (1-byte-5.001 DPT_Scaling) 10, 48, 86, 124 – Output x – Green value (1-byte-5.001 DPT_Scaling) 11, 49, 87, 125 – Output x – Blue value (1-byte-5.001 DPT_Scaling) 12, 50, 88, 126 – Output x – White value (1-byte-5.001 DPT_Scaling) 13, 51, 89, 127 – Output x – Red dimming (4-bit-3.007 DPT_Control_Dimming) 14, 52, 90, 128 – Output x – Green dimming (4-bit-3.007 DPT_Control_Dimming) 15, 53, 91, 129 – Output x – Blue dimming (4-bit-3.007 DPT_Control_Dimming) 16, 54, 92, 130 – Output x – White dimming (4-bit-3.007 DPT_Control_Dimming) 17, 55, 93, 131 – Output x – Colour scrolling (4-bit-3.007 DPT_Control_Dimming)
```



```
25, 63, 101, 139 – Output x – Status indication red value (1 byte -5.001 DPT_Scaling)
27, 65, 103, 141 – Output x – Status indication green value (1 byte -5.001 DPT_Scaling)
29, 67, 105, 143 – Output x – Status indication blue value (1 byte -5.001 DPT_Scaling)
31, 69, 107, 145 – Output x – Status indication white value (1 byte -5.001 DPT_Scaling)
32, 70, 108, 146 – Output x – Status indication RGBW values (6-byte-251.600 DPT_Colour_RGBW)
33, 71, 109, 147 – Output x – Status indication RGB values (3-byte-232.600 DPT_Colour_RGB)
```


3.1.3.3 Timer

The Timer function is used to switch on a lighting circuit for a programmable period. The timer may be interrupted before expiry of the delay time. A programmable Cut-OFF pre-warning announces the end of the delay time by halving the present brightness value of the output.



Parameter	Description	Value
Timer duration	This parameter determines the timer duration.	Not active, 1 s, 2 s, 3 s, 5 s, 10 s, 15 s, 20 s, 30 s, 45 s, 1 min, 1 min 15 s, 1 min 30 s, 2 min* , 2 min 30 s, 3 min, 5 min, 15 min, 20 min, 30 min, 1 h, 2 h, 3 h, 5 h, 12 h, 24 h
Cut-OFF pre-warning	This parameter determines the lead time of the cut-OFF pre-warning.	Not active, 15 s, 30 s* , 1 min





Tm: Timer duration
Tp: Pre-warning lead time

Note: If the lead time of the cut-OFF pre-warning is greater than the duration of the timer, the cut-OFF pre-warning is not triggered.

Communication objects:

3.1.3.4 Priority

The Priority function is used to force the output into a defined state.

Only a Priority OFF command authorizes the output for control.


At the end of the priority, the output returns to the status it had before the priority (Memorisation function).

The device responds to telegrams received via the **Priority** object, as given in the following table:

Telegram received by the priority operation object			
Hexadecimal Binary Value		Output behaviour	
Value	Bit 1 (MSB)	Bit 0 (LSB)	
00	0	0	End of the priority
01	0	1	End of the priority
02	1	0	Priority OFF
03	1	1	Priority ON

Note: For ON priority, the output is set to the last temperature and colour brightness value.





Communication objects:

11, 49, 87, 125 – Output x – Priority (2 Bit – 2.002 DPT_Bool_Control)
12, 50, 88, 126 – Output x – Status indication priority (1 Bit – 1.011 DPT_State)


3.1.3.5 Automatic control

The Automatic control function is used to command an output in parallel to the ON/OFF function. The two functions have the same level of priority. The last command received will act on the status of the output. An additional command object is used to activate or deactivate the Automatic control.

Example: when an output is controlled by a button and in parallel by an automatic control (timer, twilight switch, weather station, etc.) the automatic control can be deactivated for reasons of comfort (vacations, public holidays, etc.).








Communication objects:

- 3, 41, 79, 117 Output x ON/OFF automatic control (1 Bit 1.001 DPT_Switch)
- 4, 42, 80, 118 Output x Brightness value in % automatic control (1 Byte 5.001 DPT_Scaling)
- 5, 43, 81, 119 Output x Automatic control deactivation (1 Bit 1.001 DPT_Switch)
- 6, 44, 82, 120 Output x Automatic control deactivation status (1 Bit 1.001 DPT_Switch)



3.1.3.6 Scene

The Scene function is used to switch groups of outputs into a configurable predefined state. Each output can be included in 64 different scenes.



Parameter	Description	Value
Number of scenes used	This parameter determines the number of scenes used.	1*64

Note: If the Scene number received on the Scene object is greater than the maximum number of scenes, the status of the output remains unchanged.

Parameter	Description
Scene x	This parameter is used to activate the scene in question.

x = 1 to 64

Note: Each output has up to 64 scenes available, in accordance with the **Number of scenes used** parameter.

Depending on the channel function value, the setting parameters for the different stages may change.

■ Dimmer



Parameter	Description	Value
Brightness value	This parameter defines the brightness value that is applied to the output when Scene ${\bf x}$ is selected.	0100*

x = 1 to 64




■ Colour temperature



Parameter	Description	Value
Brightness value	This parameter defines the brightness value that is applied to the output when Scene ${\bf x}$ is selected.	0100*
Colour temperature	This parameter defines the colour temperature applied to the output when stage x is selected.	1000 5000 *10000

x = 1 to 64

■ Colour



Parameter	Description	Value
Brightness value	This parameter defines the brightness value that is applied to the output when Scene ${\bf x}$ is selected.	0100*
Colour Red/Green/Blue	This parameter defines the value of the red, green and blue components applied to the output when stage x is selected.	

x = 1 to 64

Parameter	Description	Value
Colour White	This parameter defines the value of the white component applied to the output when stage x is selected.	0 255 *


x = 1 to 64

Note: This parameter is only visible when the **Colour components** parameter has the value: **Red/Green/Blue/White**.

Note: By clicking the symbol, a window opens to allow the colours to be adjusted.







Learning and storing scenes

This process is used to change and store a scene. For example, by locally pressing the key in the room or by emission of the values from a visualization.


To access and store scenes, the following values must be sent:

Scene number	Access scene (Object value: 1 byte)	Store scene (Object value: 1 byte)
1-64	= Scene number -1	= Scene number +128
Examples		
1	0	128
2	1	129
3	2	130
64	63	191

Here is the scene memorisation for local switches, for example.


- · Activate scene by briefly pressing the transmitter that starts it.
- The outputs (lights, shutters, etc.) are set in the desired state using the usual local control devices (buttons, remote control, etc.).
- Memorise the status of the outputs with a press greater than 5 seconds long on the transmitter that starts the scene. The memorisation can be displayed by short-term activation of the outputs.





3.1.4 DALI

This part configures the parameters related to the DALI bus. They are valid for all of the output channels.




■ Dimming curve

During dimming, the evolution of the logarithmic characteristic curve, planned for DALI and saved in the equipment, is not adapted for dimming controls.

This is why the product offers the option of influencing the DALI dimming characteristic curve without intervening in the equipment.

Linear: The product linearises the dimming characteristic curve by converting all of the brightness values received by the KNX system under an appropriate form in DALI data values. The KNX brightness values are reproduced linearly in this way on the luminous flux emitted by the DALI light sources. The product does not perform any linear dimming on this setting. It is only once the non-linear conversion of the product is combined with the logarithmic characteristic curve of equipment that a linear graduation of the luminous flux related to the physical output of a piece of equipment ensues.

The brightness value status indications to the KNX system are also adjusted by conversion.




* Default value



Logarithmic: The product transmits the KNX brightness values almost without input from the DALI interface side. The data values only lead to a levelling in the lower dimming range. Once the transmission of values by the product is combined with the logarithmic characteristic curve of equipment, a logarithmic graduation of the luminous flux related to the physical output of a piece of equipment ensues.

The status indication of the actual DALI brightness value to the KNX system is also possible.





KNX of 8 bit data value [0...255]

Parameter	Description	Value
Dimming curve	This parameter defines the order of magnitude of the values for	Linear
	transmitting the data between the KNX and DALI bus.	Logarithmic*

■ Emission of DALI settings

Parameter	Description	Value
Emission of DALI	The parameters concerning the DALI settings are emitted:	
settings	- When starting the product.	At initialization*
	- Periodically after a configurable time.	Periodically
	When starting the product and periodically according to a set time.	At initialization and periodically

Parameter	Description	Value
Periodicity	This parameter determines the time interval between each emission of the DALI settings to the ballasts.	00:00* 18 :12 (mm:ss)

Note: This parameter is only visible when the **At initialization and periodically** parameter has the value: **Periodically** or **At initialization and periodically**.



3.2 Communication objects

3.2.1 Communication objects dimmer

	Number	Name	Function of the object	Length	С	R	W	T
= ≵I	0	Output 1	ON/OFF	1 bit	С	-	W	-
= ≵I	1	Output 1	Dimming	4 bit	С	-	W	-
■ ≵I	2	Output 1	Brightness value	1 byte	С	-	W	-
= ≵I	3	Output 1	ON/OFF automatic control	1 bit	С	-	W	-
- ≵	4	Output 1	Brightness value in % automatic control	1 byte	С	-	W	-
= ≵I	5	Output 1	Automatic control deactivation	1 bit	С	-	W	-
■ ≵I	6	Output 1	Automatic control deactivation status	1 bit	С	R	-	Т
= ≵I	7	Output 1	Status indication ON/OFF	1 bit	С	R	-	Т
■ ≵	8	Output 1	Status ind. brightness value	1 byte	С	R	-	Т
<u>-</u> ≵I	9	Output 1	Timer	1 bit	С	-	W	-
■ ≵	10	Output 1	Scene	1 byte	С	-	W	-
= ≵I	11	Output 1	Priority	2 bit	С	-	W	-
■ ≵I	12	Output 1	Status indication priority	1 bit	С	R	-	Т

3.2.1.1 ON/OFF

No.	Name		Data type	Flags
0, 38, 76, 114	Output x	ON/OFF	1 bit - 1.001 DPT_Switch	C, W

These objects are always activated.

It allows the output channel to be switched depending on the value sent on the KNX bus.

Normally open:

- Upon reception of an OFF command, the output varies the brightness value 0%.
- Upon reception of an ON command, the output varies to the last brightness value received (1 to 100%).



3.2.1.2 Dimming

No.	Name	Function of the object	Data type	Flags
1, 39, 77, 115	Output x	, 5	4 bit - 3.007 DPT_Control_Dimming	C, W

These objects are always activated. It allows for relative dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed in accordance with the 4-bit format value that arrives.

Object value:

b3	b2	b1	b0
С		Steps	

Data fields	Description	Code
С	Increase or reduction in brightness	0: Decrease 1: Increase
Steps	Brightness between 0% and 100% divided into steps	0: Stop 1: 100% 2: 50% 3: 25% 4: 12% 5: 6% 6: 3% 7: 1%

No.	Name	Function of the object	Data type	Flags
2, 40, 78, 116	Output x	Brightness value	1 byte - 5.001 DPT_Scaling	C, W

These objects are always activated. It allows for absolute dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the brightness value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.



3.2.1.3 Automatic control

No.	Name	Function of the object	Data type	Flags
3, 41, 79, 117	Output x	ON/OFF automatic control	1 bit - 1.001 DPT_Switch	C, W

This object is activated when the **Automatic control** parameter is active. It allows the output channel to be switched depending on the value sent on the KNX bus.

Normally open:

- Upon reception of an OFF command, the output varies the brightness value 0%.
- Upon reception of an ON command, the output varies to the last brightness value received (1 to 100%).

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags
4, 42, 80, 118	Output x	Brightness value in % automatic control	1 byte - 5.001 DPT_Scaling	C, W

This object is activated when the **Automatic control** parameter is active. It allows for absolute dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the brightness value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags
5, 43, 81, 119	Output x	Automatic control deactivation	1 bit - 1.003 DPT_Enable	C, W

This object is activated when the **Automatic control deactivation** parameter is active.

This object is used to activate the automatic control function.

Object value:

- If the object receives the value 0, the automatic control function is inactive.
- If the object receives the value 1, the automatic control function is active.

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags
6, 44, 82, 120	Output x	Automatic control deactivation status	1 bit - 1.011 DPT_State	C, R, T

This object is activated when the **Automatic control deactivation** parameter is active.

This object is used to send the status of the Automatic control deactivation function of the device on the KNX bus.

Object value:

- If the Automatic control deactivation function is deactivated, a telegram with a logical value 0 is sent.
- If the Automatic control deactivation function is activated, a telegram with a logical value 1 is sent.

This object is sent when there is a status change.

For further information, see: Automatic control.



3.2.1.4 Status indication

No.	Name	Function of the object	Data type	Flags
7, 45, 83, 121	Output x	Status indication ON/OFF	1 bit - 1.001 DPT_Switch	C, R, T

These objects are always activated.

This object is used to send the switching status of the appliance output channel on the KNX bus.

Object value:

- If the output relay is open, a telegram with logic value 0 is sent on the KNX bus.
- If the output relay is closed, a telegram with logic value 1 is sent on the KNX bus.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
8, 46, 84, 122	Output x	Status ind. brightness value	1 byte - 5.001 DPT_Scaling	C, R, T

These objects are always activated.

This object allows the status of the brightness value of the Output to be sent over the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.

3.2.1.5 Timer

No.	Name	Function of the object	Data type	Flags
9, 47, 85, 123	Output x	Timer	1 bit - 1.010 DPT_Start	C, W

This object is activated when the **Timer** parameter is active.

This object is used to activate the Timer function of the device via the KNX bus.

Object value:

- If a rising edge (0 to 1) arrives at this object, the output switches for a configurable period.
- If a falling edge (1 to 0) arrives at this object, the output remains in its current state.

Note: The timer duration can be interrupted by a long press on the button controlling the timer.

Note: When a start command is received during the timer, the timer duration is reset.

For further information, see: Timer.



3.2.1.6 Scene

No.	Name	Function of the object	Data type	Flags
10, 48, 86, 124	Output x	Scene	1 byte - 18.001 DPT_SceneControl	C, W

This object is activated when the **Scene** parameter is active.

This object is used to recall or save a scene.

Details on the format of the object are given below.

7	6	5	4	3	2	1	0
Learning	Not used	Scene number					

Bit 7: 0: The scene is called / 1: The scene is saved.

Bit 6: Not used.

Bit 5 to Bit 0: Scene numbers from 0 (Scene 1) to 63 (Scene 64).

For further information, see: <u>Scene</u>.

3.2.1.7 Priority

No.	Name	Function of the object	Data type	Flags
11, 49, 87, 125	Output x	Priority	2 bit - 2.002 DPT_Bool_Control	C, W

This object is activated if the **Priority** parameter is active.

The status of the output contact is determined directly by this object.

Details on the format of the object are given below.

Telegram received by the priority operation object			Outrout hash as issue
Hexadecimal	al Binary Value		Output behaviour
Value	Bit 1 (MSB)	Bit 0 (LSB)	
00	0	0	End of the priority
01	0	1	End of the priority
02	1	0	Priority OFF
03	1	1	Priority ON

The first bit of this object (Bit 0) determines the status of the output contact, which should be priority controlled. The second bit activates or deactivates the Priority.

For further information, see: Priority.



No.	Name	Function of the object	ction of the object Data type	
12, 50, 88, 126	Output x	Status indication priority	1 bit - 1.011 DPT_State	C, R, T

This object is activated if the **Priority** parameter is active.

This object allows the status of the Priority to be sent from the device on the KNX bus.

Object value:

0 = Not forced, 1 = Forced:

- If Priority is deactivated, a telegram is sent with logic value 0.
- If Priority is activated, a telegram is sent with logic value 1.

This object is sent when there is a status change.

For further information, see: Priority.



3.2.2 Communication objects colour temperature

	Number	Name	Function of the object	Length	С	R	W	Т
= ≵I	0	Output 1	ON/OFF	1 bit	С	-	W	-
= ≵I	1	Output 1	Dimming	4 bit	С	-	W	-
= ≵	2	Output 1	Brightness value	1 byte	С	-	W	-
= ≵I	3	Output 1	Dimming colour temperature	4 bit	С	-	W	-
= ≵	4	Output 1	Colour temperature in K	2 byte	С	-	W	-
= ≵I	5	Output 1	Colour temperature in %	1 byte	С	-	W	-
= ≵	6	Output 1	ON/OFF automatic control	1 bit	С	-	W	-
= ≵I	7	Output 1	Brightness value in % automatic control	1 byte	С	-	W	-
= ≵	8	Output 1	Automatic control deactivation	1 bit	С	-	W	-
= ≵I	9	Output 1	Automatic control deactivation status	1 bit	С	R	-	Т
= ≵	10	Output 1	Status indication ON/OFF	1 bit	С	R	-	Т
= ≵I	11	Output 1	Status ind. brightness value	1 byte	С	R	-	Т
<u>-</u> ≱	12	Output 1	Status indication colour temperature in %	1 byte	С	R	-	Т
= ≵l	13	Output 1	Status indication colour temperature in K	2 byte	С	R	-	Т
= ≵	14	Output 1	Timer	1 bit	С	-	W	-
=	15	Output 1	Scene	1 byte	С	-	W	-
= ≵	16	Output 1	Priority	2 bit	С	-	W	-
= ≵I	17	Output 1	Status indication priority	1 bit	С	R	-	Т

3.2.2.1 ON/OFF

No.	Name	Function of the object	Data type	Flags
0, 38, 76, 114	Output x	ON/OFF	1 bit - 1.001 DPT_Switch	C, W

These objects are always activated.

It allows the output channel to be switched depending on the value sent on the KNX bus.

Normally open:

- Upon reception of an OFF command, the output varies the brightness value 0%.
 Upon reception of an ON command, the output varies to the last brightness value received (1 to 100%).



3.2.2.2 Dimming

No.	Name	Function of the object	Data type	Flags
1, 39, 77, 115	Output x	3	4 bit - 3.007 DPT_Control_Dimming	C, W

These objects are always activated. It allows for relative dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed in accordance with the 4-bit format value that arrives.

Object value:

b3	b2	b1	b0
С		Steps	

Data fields	Description	Code
С	Increase or reduction in brightness	0: Decrease 1: Increase
Steps	Brightness between 0% and 100% divided into steps	0: Stop 1: 100% 2: 50% 3: 25% 4: 12% 5: 6% 6: 3% 7: 1%

No.	Name	Function of the object	Data type	Flags
2, 40, 78, 116	Output x	Brightness value	1 byte - 5.001 DPT_Scaling	C, W

These objects are always activated. It allows for absolute dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the brightness value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.



3.2.2.3 Colour temperature

No.	Name	Function of the object	Data type	Flags
3, 41, 79, 117	Output x	3	4 bit - 3.007 DPT_Control_Dimming	C, W

This object is activated when the parameter **Channel function** has the value **Colour temperature**. It allows the colour temperature to be dimmed depending on the value sent on the KNX bus.

The output is dimmed in accordance with the 4-bit format value that arrives.

Object value:

b3	b2	b1	b0
С		Steps	

Data fields	Description	Code
С	Increase or reduction in brightness	0: Decrease 1: Increase
Steps	Brightness between 0% and 100% divided into steps	0: Stop 1-7: 100%

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
4, 42, 80, 118	Output x		2 - byte - 7.600 DPT_Absolute_Colour_Temp erature	C, W

This object is activated when the parameter **Channel function** has the value **Colour temperature**.

It allows the colour temperature to be dimmed depending on the value sent on the KNX bus.

The output is dimmed according to the value that arrives in 2-byte format and corresponds in °K to the colour temperature value to be attained.

Object value: 0 to 65535 °K.

For further information, see: Additional parameters.



No.	Name	Function of the object	Data type	Flags
5, 43, 81, 119	Output x	Colour temperature in %	1 - byte - 5.001 DPT_Scaling	C, W

This object is activated when the parameter **Channel function** has the value **Colour temperature**.

It allows the colour temperature to be dimmed depending on the value sent on the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the colour temperature value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

Note: 0% corresponds to the minimum value that can be set and 100% corresponds to the maximum value that can

be set.

For further information, see: Additional parameters.

3.2.2.4 Automatic control

No.	Name	Function of the object	Data type	Flags
6, 44, 82, 120	Output x	ON/OFF automatic control	1 bit - 1.001 DPT_Switch	C, W

This object is activated when the **Automatic control** parameter is active. It allows the output channel to be switched depending on the value sent on the KNX bus.

Normally open:

- Upon reception of an OFF command, the output varies the brightness value 0%.
- Upon reception of an ON command, the output varies to the last brightness value received (1 to 100%).

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags	
7, 45, 83, 12	21 Output x	Brightness value in % automatic control	1 byte - 5.001 DPT_Scaling	C, W	

This object is activated when the **Automatic control** parameter is active. It allows for absolute dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the brightness value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags
8, 46, 84, 122	Output x	Automatic control deactivation	1 bit - 1.003 DPT_Enable	C, W

This object is activated when the Automatic control deactivation parameter is active.

This object is used to activate the automatic control function.

Object value:

- If the object receives the value 0, the automatic control function is inactive.
- If the object receives the value 1, the automatic control function is active.

For further information, see: Automatic control.



No.	Name	Function of the object	Data type	Flags
9, 47, 85, 123	Output x	Automatic control deactivation status	1 bit - 1.011 DPT_State	C, R, T

This object is activated when the Automatic control deactivation parameter is active.

This object is used to send the status of the Automatic control deactivation function of the device on the KNX bus.

Object value:

- If the Automatic control deactivation function is deactivated, a telegram with a logical value 0 is sent.
- If the Automatic control deactivation function is activated, a telegram with a logical value 1 is sent.

This object is sent when there is a status change.

For further information, see: Automatic control.

3.2.2.5 Status indication

No.	Name	Function of the object	Data type	Flags
10, 48, 86, 124	Output x	Status indication ON/OFF	1 bit - 1.001 DPT_Switch	C, R, T

These objects are always activated.

This object is used to send the switching status of the appliance output channel on the KNX bus.

Object value:

- If the output relay is open, a telegram with logic value 0 is sent on the KNX bus.
- If the output relay is closed, a telegram with logic value 1 is sent on the KNX bus.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
11, 49, 87, 125	Output x	Status ind. brightness value	1 byte - 5.001 DPT_Scaling	C, R, T

These objects are always activated.

This object allows the status of the brightness value of the Output to be sent over the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
12, 50, 88, 126	1	Status indication colour temperature in %	1 byte - 5.001 DPT_Scaling	C, R, T

This object is activated when the parameter Channel function has the value Colour temperature.

This object is used to emit the colour temperature value of the output on the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Note: 0% corresponds to the minimum value that can be set and 100% corresponds to the maximum value that can be set.

This object is sent when there is a status change.



No.	Name	Function of the object	Data type	Flags
13, 51, 89, 127	Output x		2 byte - 7.600 DPT_Absolute_Colour_Temp erature	C, R, T

This object is used to emit the colour temperature value of the output on the KNX bus.

Object value: 0 to 65535 °K.

This object is sent when there is a status change.

3.2.2.6 Timer

No.	Name	Function of the object	Data type	Flags	
14, 52, 90, 128	Output x	Timer	1 bit - 1.010 DPT_Start	C, W	

This object is activated when the **Timer** parameter is active.

This object is used to activate the Timer function of the device via the KNX bus.

Object value:

- If a rising edge (0 to 1) arrives at this object, the output switches for a configurable period.
- If a falling edge (1 to 0) arrives at this object, the output remains in its current state.

Note: The timer duration can be interrupted by a long press on the button controlling the timer.

Note: When a start command is received during the timer, the timer duration is reset.

For further information, see: Timer.

3.2.2.7 Scene

No.	Name	Function of the object	Data type	Flags
15, 53, 91, 129	Output x	Scene	1 byte - 18.001 DPT_SceneControl	C, W

This object is activated when the **Scene** parameter is active.

This object is used to recall or save a scene.

Details on the format of the object are given below.

7	6	5	4	3	2	1	0
Learning	Not used	Scene number					

Bit 7: 0: The scene is called / 1: The scene is saved.

Bit 6: Not used.

Bit 5 to Bit 0: Scene numbers from 0 (Scene 1) to 63 (Scene 64).

For further information, see: Scene.



3.2.2.8 Priority

No.	Name	Function of the object	Data type	Flags
16, 54, 92, 130	Output x		2 bit - 2.002 DPT_Bool_Control	C, W

This object is activated if the **Priority** parameter is active.

The status of the output contact is determined directly by this object.

Details on the format of the object are given below.

Telegram received by the priority operation object			
Hexadecimal	Hexadecimal Binary Value		Output behaviour
Value	Bit 1 (MSB) Bit 0 (LSB)		
00	0	0	End of the priority
01	0	1	End of the priority
02	1	0	Priority OFF
03	1	1	Priority ON

The first bit of this object (Bit 0) determines the status of the output contact, which should be priority controlled. The second bit activates or deactivates the Priority.

For further information, see: Priority.

No.	Name	Function of the object	Data type	Flags
17, 55, 93, 131	Output x	Status indication priority	1 bit - 1.011 DPT_State	C, R, T

This object is activated if the **Priority** parameter is active.

This object allows the status of the Priority to be sent from the device on the KNX bus.

Object value:

0 = Not forced, 1 = Forced:

- If Priority is deactivated, a telegram is sent with logic value 0.
- If Priority is activated, a telegram is sent with logic value 1.

This object is sent when there is a status change.

For further information, see: Priority.



3.2.3 Colour communication objects

	Number	Name	Function of the object	Length	С	R	W	Т
■ ≵	0	Output 1	ON/OFF	1 bit	С	-	W	-
- ≵I	1	Output 1	Dimming	4 bit	С	-	W	-
■ ≵I	2	Output 1	Brightness value	1 byte	С	-	W	-
- ≵I	7	Output 1	RGBW values	6 byte	С	-	W	-
- ≵	8	Output 1	RGB values	3 byte	С	-	W	-
- ≵I	9	Output 1	Red value	1 byte	С	-	W	-
- ≵	10	Output 1	Green value	1 byte	С	-	W	-
= ≵I	11	Output 1	Blue value	1 byte	С	-	W	-
- ≵	12	Output 1	White value	1 byte	С	-	W	-
= ≵I	13	Output 1	Red dimming	4 bit	С	-	W	-
- ≵	14	Output 1	Green dimming	4 bit	С	-	W	-
= ≵I	15	Output 1	Blue dimming	4 bit	С	-	W	-
- ≵	16	Output 1	White dimming	4 bit	С	-	W	-
= ≵I	17	Output 1	Colour scrolling	4 bit	С	-	W	-
- ≵	18	Output 1	ON/OFF automatic control	1 bit	С	-	W	-
= ≵I	19	Output 1	Brightness value in % automatic control	1 byte	С	-	W	-
- ≵	20	Output 1	Automatic control deactivation	1 bit	С	-	W	-
= ≵I	21	Output 1	Automatic control deactivation status	1 bit	С	R	-	Т
- ≵	22	Output 1	Status indication ON/OFF	1 bit	С	R	-	Т
= ≵I	23	Output 1	Status ind. brightness value	1 byte	С	R	-	Т
- ≵	25	Output 1	Status indication red value	1 byte	С	R	-	Т
= ≵I	27	Output 1	Status indication green value	1 byte	С	R	-	Т
= ≵I	29	Output 1	Status indication blue value	1 byte	С	R	-	Т
- ≵I	31	Output 1	Status indication white value	1 byte	С	R	-	T
= ≵I	32	Output 1	Status indication RGBW values	6 byte	С	R	-	Т
■ ≵I	33	Output 1	Status indication RGB values	3 byte	С	R	-	T
= ≵I	34	Output 1	Priority	1 bit	С	-	W	-
■ ≵I	35	Output 1	Status indication priority	1 byte	С	-	W	-
■ ≵I	36	Output 1	Priority	2 bit	С	-	W	-
- ≵I	37	Output 1	Status indication priority	1 bit	С	R	-	Т



3.2.3.1 ON/OFF

No.	Name	Function of the object	on of the object Data type	
0, 38, 76, 114	Output x	ON/OFF	1 bit - 1.001 DPT_Switch	C, W

These objects are always activated.

It allows the output channel to be switched depending on the value sent on the KNX bus.

Normally open:

- Upon reception of an OFF command, the output varies the brightness value 0%.
- Upon reception of an ON command, the output varies to the last brightness value received (1 to 100%).

3.2.3.2 Dimming

No.	Name	Function of the object	Data type	Flags
1, 39, 77, 115	Output x	3	4 bit - 3.007 DPT_Control_Dimming	C, W

These objects are always activated. It allows for relative dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed in accordance with the 4-bit format value that arrives.

Object value:

b3	b2	b1	b0	
С	Steps			

Data fields	Description	Code
С	Increase or reduction in brightness	0: Decrease 1: Increase
Steps	Brightness between 0% and 100% divided into steps	0: Stop 1: 100% 2: 50% 3: 25% 4: 12% 5: 6% 6: 3% 7: 1%



No.	Name	Function of the object	Data type	Flags
2, 40, 78, 116	Output x	Brightness value	1 byte - 5.001 DPT_Scaling	C, W

These objects are always activated. It allows for absolute dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the brightness value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

3.2.3.3 Colour

No.	Name	Function of the object	Data type	Flags
7, 45, 83, 121	Output x	RGBW values	6 byte - 251.600	C, W
			DPT_Colour_RGBW	

This object is activated when the **Channel function** parameter has the **Colour** value and when the **Colour** components parameter has the value **Red/Green/Blue/White**.

It enables absolute dimming of the output channel depending on the value sent on the KNX bus. This command is valid for the red, green, blue and white coloured components.

Object value:

Byte 6 (MSB)					Byte 5					Byte 4											
Red									Gre	en							ВІ	ue			
0 0 0 0 0 0 0 0				U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	

Byte 3 (LSB)							Byte 2						Byte 1 (LSB)							
White									Rese	erved				Reserved				Dimming		
U U U U U U U U			U	r	r	r	r	r	r	r	r	r	r	r	r	R	G	В	W	

Fields	Designation	Value
Red	Red colour level	0 to 255 (8 bit)
Green	Green colour level	0 to 255 (8 bit)
Blue	Blue colour level	0 to 255 (8 bit)
White	White colour level	0 to 255 (8 bit)
R	Approval of the red coloured value	0 or 1
G	Approval of the green coloured value	0 or 1
В	Approval of the blue coloured value	0 or 1
W	Approval of the white coloured value	0 or 1



No.	Name	Function of the object	Data type	Flags
8, 46, 84, 122	Output x	RGB values	3 byte - 232.600	C, W
			DPT_Colour_RGB	

This object is activated when the **Channel function** parameter has the **Colour** value and when the **Colour** components parameter has the value **Red/Green/Blue**.

It enables absolute dimming of the output channel depending on the value sent on the KNX bus. This command is valid for the red, green and blue coloured components.

Object value:

Byte 3 (MSB)						Byte 2					Byte 1 (LSB)										
Red									Gre	en							Bl	ue			
0 0 0 0 0 0 0 0				U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	

Fields	Designation	Value
Red	Red colour level	0 to 255 (8 bit)
Green	Green colour level	0 to 255 (8 bit)
Blue	Blue colour level	0 to 255 (8 bit)

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
9, 47, 85, 123	Output x	Red value	1 byte - 5.001 DPT_Scaling	C, W

This object is activated when the parameter Channel function has the value Colour.

It enables absolute dimming of the output channel depending on the value sent on the KNX bus.

This control is only valid for the red coloured component.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
10, 48, 86, 124	Output x	Green value	8 bit - 5.001 DPT_Scaling	C, W

This object is activated when the parameter **Channel function** has the value **Colour**.

It enables absolute dimming of the output channel depending on the value sent on the KNX bus.

This command is only valid for the green coloured component.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.



No.	Name	Function of the object	Data type	Flags
11, 49, 87, 125	Output x	Blue value	1 byte - 5.001 DPT_Scaling	C, W

It enables absolute dimming of the output channel depending on the value sent on the KNX bus.

This command is only valid for the blue coloured component.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
12, 50, 88, 126	Output x	White value	1 byte - 5.001 DPT_Scaling	C, W

This object is activated when the **Channel function** parameter has the **Colour** value and when the **Colour** components parameter has the value **Red/Green/Blue/White**.

It enables absolute dimming of the output channel depending on the value sent on the KNX bus.

This command is only valid for the white coloured component.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
13, 51, 89, 127	Output x		4 bit - 3.007 DPT_Control_Dimming	C, W

This object is activated when the parameter **Channel function** has the value **Colour**.

It enables relative dimming of the output channel depending on the value sent on the KNX bus.

This control is only valid for the red coloured component.

Object value:

b3	b2	b1	b0
С		Steps	

Data fields	Description	Code
С	Increase or reduction in brightness	0: Decrease 1: Increase
Steps	Brightness between 0% and 100% divided into steps	0: Stop 1: 100% 2: 50% 3: 25% 4: 12% 5: 6% 6: 3% 7: 1%



No.	Name	Function of the object	Data type	Flags
14, 52, 90, 128	Output x		4 bit - 3.007 DPT_Control_Dimming	C, W

It enables relative dimming of the output channel depending on the value sent on the KNX bus.

This command is only valid for the green coloured component.

Object value: See object No. 13.

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
15, 53, 91, 129	Output x	Blue dimming	4 bit - 3.007 DPT_Control_Dimming	C, W

This object is activated when the parameter Channel function has the value Colour.

It enables relative dimming of the output channel depending on the value sent on the KNX bus.

This command is only valid for the blue coloured component.

Object value: See object No. 13.

For further information, see: Additional parameters.

No.	Name	Function of the object	Data type	Flags
16, 54, 92, 130	Output x	"""	4 bit - 3.007 DPT_Control_Dimming	C, W

This object is activated when the **Channel function** parameter has the **Colour** value and when the **Colour** components parameter has the value **Red/Green/Blue/White**.

It enables relative dimming of the output channel depending on the value sent on the KNX bus.

This command is only valid for the white coloured component.

Object value: See object No. 13.



No.	Name	Function of the object	Data type	Flags
17, 55, 93, 131	Output x		4 bit - 3.007 DPT_Control_Dimming	C, W

It enables colour scrolling of the output channel depending on the value sent on the KNX bus.

Object value:

b3	b2	b1	b0
С		Steps	

Data fields	Description	Code
С	Increase or reduction in brightness	0: Rearward scrolling 1: Forward scrolling
Steps	Brightness between 0% and 100% divided into steps	0: Stop 1 - 7: Scrolling

Scrolling colours allows you to select a pre-defined colour to be applied to the output.

In addition to white, the available color set is as follows:



For further information, see: Additional parameters.

3.2.3.4 Automatic control

No.	Name	Function of the object	Data type	Flags
18, 56, 94, 132	Output x	ON/OFF automatic control	1 bit - 1.001 DPT_Switch	C, W

This object is activated when the **Automatic control** parameter is active. It allows the output channel to be switched depending on the value sent on the KNX bus.

Normally open:

- Upon reception of an OFF command, the output varies the brightness value 0%.
- Upon reception of an ON command, the output varies to the last brightness value received (1 to 100%).

For further information, see: Automatic control.



No.	Name	Function of the object	Data type	Flags
19, 57, 95, 133	Output x	Brightness value in % automatic control	1 byte - 5.001 DPT_Scaling	C, W

This object is activated when the **Automatic control** parameter is active. It allows for absolute dimming of the output as a function of the value sent by the KNX bus.

The output is dimmed according to the value that arrives in 1-byte format and corresponds in % to the brightness value to be attained.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

Resolution: Approx. 0.4%.

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags
20, 58, 96, 134	Output x	Automatic control deactivation	1 bit - 1.003 DPT_Enable	C, W

This object is activated when the **Automatic control deactivation** parameter is active.

This object is used to activate the automatic control function.

Object value:

- If the object receives the value 0, the automatic control function is inactive.
- If the object receives the value 1, the automatic control function is active.

For further information, see: Automatic control.

No.	Name	Function of the object	Data type	Flags
21, 59, 97, 135	Output x	Automatic control deactivation status	1 bit - 1.011 DPT_State	C, R, T

This object is activated when the Automatic control deactivation parameter is active.

This object is used to send the status of the Automatic control deactivation function of the device on the KNX bus.

Object value:

- If the Automatic control deactivation function is deactivated, a telegram with a logical value 0 is sent.
- If the Automatic control deactivation function is activated, a telegram with a logical value 1 is sent.

This object is sent when there is a status change.

For further information, see: Automatic control.

3.2.3.5 Status indication

No.	Name	Function of the object	Data type	Flags
22, 60, 98, 136	Output x	Status indication ON/OFF	1 bit - 1.001 DPT_Switch	C, R, T

These objects are always activated.

This object is used to send the switching status of the appliance output channel on the KNX bus.

Object value:

- If the output relay is open, a telegram with logic value 0 is sent on the KNX bus.
- If the output relay is closed, a telegram with logic value 1 is sent on the KNX bus.

This object is sent when there is a status change.



No.	Name	Function of the object	Data type	Flags
23, 61, 99, 137	Output x	Status ind. brightness value	1 byte - 5.001 DPT_Scaling	C, R, T

These objects are always activated.

This object allows the status of the brightness value of the Output to be sent over the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
25, 63, 101, 139	Output x	Status indication red value	1 byte - 5.001 DPT_Scaling	C, R, T

This object is activated when the parameter Channel function has the value Colour.

This object is used to send the status of the brightness value of the output channel for the red coloured component on the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
27, 65, 103, 141	Output x	Status indication green value	1 byte - 5.001 DPT_Scaling	C, R, T

This object is activated when the parameter Channel function has the value Colour.

This object is used to send the brightness value status of the output channel for the green coloured component on the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
29, 67, 105, 143	Output x	Status indication blue value	1 byte - 5.001 DPT_Scaling	C, R, T

This object is activated when the parameter Channel function has the value Colour.

This object is used to send the brightness value status of the output channel for the blue coloured component on the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.



No.	Name	Function of the object	Data type	Flags
31, 69, 107, 145	Output x	Status indication white value	1 byte - 5.001 DPT_Scaling	C, R, T

This object is used to send the brightness value status of the output channel for the white coloured component on the KNX bus.

Object value: 0 to 255: 0 = 0%, 255 = 100%.

This object is sent when there is a status change.

No.	Name	Function of the object	Data type	Flags
32, 70, 108,	Output x	Status indication RGBW	6 byte - 251.600	C, R, T
146		values	DPT Colour RGBW	

This object is activated when the **Channel function** parameter has the **Colour** value and when the **Colour** components parameter has the value **Red/Green/Blue/White**.

This object is used to send the brightness value status of the output channel for the red, green, blue and white coloured components on the KNX bus.

Object value:

Byte 6 (MSB)						Byte 5					Byte 4												
Red Green						Blue																	
U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	J	U	U	U	U	U	U	U

		В	yte 3	(LS	В)						Byt	te 2				Byte 1 (LSB)							
	White Reserved						Reserved Dim			Dimi	nming												
U	U	U	U	U	U	U	U	r	r	r	r	r	r	r	r	r	r	r	r	R	G	В	W

Fields	Designation	Value
Red	Red colour level	0 to 255 (8 bit)
Green	Green colour level	0 to 255 (8 bit)
Blue	Blue colour level	0 to 255 (8 bit)
White	White colour level	0 to 255 (8 bit)
R	Approval of the red coloured value	0 or 1
G	Approval of the green coloured value	0 or 1
В	Approval of the blue coloured value	0 or 1
W	Approval of the white coloured value	0 or 1

This object is sent when there is a status change.



No.	Name	Function of the object	Data type	Flags
33, 71, 109,	Output x	Status indication RGB values	3 byte - 232.600	C, R, T
147			DPT_Colour_RGB	

This object is activated when the **Channel function** parameter has the **Colour** value and when the **Colour** components parameter has the value **Red/Green/Blue**.

This object is used to send the brightness value status of the output channel for the red, green and blue coloured components on the KNX bus.

Object value:

Byte 3 (MSB)						Byt	e 2				Byte 1 (LSB)												
Red			Green				Blue																
U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U

Fields	Designation	Value
Red	Red colour level	0 to 255 (8 bit)
Green	Green colour level	0 to 255 (8 bit)
Blue	Blue colour level	0 to 255 (8 bit)

This object is sent when there is a status change.

3.2.3.6 Timer

No.	Name	Function of the object	Data type	Flags
34, 72, 110, 148	Output x	Timer	1 bit - 1.010 DPT_Start	C, W

This object is activated when the **Timer** parameter is active.

This object is used to activate the Timer function of the device via the KNX bus.

Object value:

- If a rising edge (0 to 1) arrives at this object, the output switches for a configurable period.
- If a falling edge (1 to 0) arrives at this object, the output remains in its current state.

Note: The timer duration can be interrupted by a long press on the button controlling the timer.

Note: When a start command is received during the timer, the timer duration is reset.

For further information, see: Timer.



3.2.3.7 Scene

No.	Name	Function of the object	Data type	Flags
35, 73, 111, 149	Output x	Scene	1 byte - 18.001 DPT_SceneControl	C, W

This object is activated when the **Scene** parameter is active.

This object is used to recall or save a scene.

Details on the format of the object are given below.

7	6	5	4	3	2	1	0
Learning	Not used		5	Scene	numbe	r	

Bit 7: 0: The scene is called / 1: The scene is saved.

Bit 6: Not used.

Bit 5 to Bit 0: Scene numbers from 0 (Scene 1) to 63 (Scene 64).

For further information, see: Scene.

3.2.3.8 Priority

No.	Name	Function of the object	Data type	Flags
36, 74, 112, 150	Output x		2 bit - 2.002 DPT_Bool_Control	C, W

This object is activated if the **Priority** parameter is active.

The status of the output contact is determined directly by this object.

Details on the format of the object are given below.

Telegram re	ceived by the pric	ority operation			
Hexadecimal	Binary	Value	Output behaviour		
Value	Bit 1 (MSB) Bit 0 (LSB)		7		
00	0	0	End of the priority		
01	0	1	End of the priority		
02	1	0	Priority OFF		
03	1	1	Priority ON		

The first bit of this object (Bit 0) determines the status of the output contact, which should be priority controlled. The second bit activates or deactivates the Priority.

For further information, see: Priority.



No.	Name	Function of the object	Data type	Flags
37, 75, 113, 151	Output x	Status indication priority	1 bit - 1.011 DPT_State	C, R, T

This object is activated if the **Priority** parameter is active.

This object allows the status of the Priority to be sent from the device on the KNX bus.

Object value:

0 = Not forced, 1 = Forced:

- If Priority is deactivated, a telegram is sent with logic value 0.
- If Priority is activated, a telegram is sent with logic value 1.

This object is sent when there is a status change.

For further information, see: Priority.



4 Programming by Easy Tool


4.1 Product overview

■ TXA 664D: 4 outputs DALI broadcast

Product view:



View of channels:



4-fold output					
-6	TXA664D - 1 - 1 Housing - Dimming				
-	TXA664D - 1 - 2 Housing - Dimming				
-6	TXA664D - 1 - 3 Housing - Dimming				
-6	TXA664D - 1 - 4 Housing - Dimming				

■ Product settings

This configuration window is used for general configuration of the device.





This configuration window is used to set the operating mode of the output channel. Depending on the operating mode, the icon symbolising the output changes.

Symbols	- <u>ç</u>	₹	- À-€
Operating mode	Dimmer	Colour	Colour temperature




Note: All available functions are valid for all operating modes, except the colour dimming and colour temperature setting, each having an additional function.


■ Pathway parameters

This parameter window is used to set the device outputs. These parameters are available individually for each output.

- Dimmer and colour channel



- Colour temperature channel





■ Available functionalities: For all operating modes

Lighting	Dimming			
ON	Increase dimming/ON			
OFF	Decrease dimming/OFF			
ON/OFF	Increase/decrease dimming			
Toggle switch	Dimming			
Timer	Dimming switch			
Priority ON	Dimming automatic control PB			
Priority OFF	Dimmer switch automatic control			
Priority ON push-button (1)	Scene			
Priority OFF push-button (1)	Scene switch			
Automatic control ON	Automatic control deactivation			
Automatic control OFF	Automatic control deactivation toggle (1)			
ON/OFF automatic control				
Scene				
Scene switch				
Automatic control deactivation				
Automatic control deactivation toggle (1)				

⁽¹⁾ These functionalities are only available with products with push-button input that have status indication LEDs.



■ Additional functions: For the colour operating mode

Dimmi	Dimming					
3	Forward colour scrolling					
3	Rearward colour scrolling					

■ Additional functions: For the colour temperature operating mode

Dimming	
-A	Colour temperature increase
- À-	Colour temperature decrease




4.2 Product functionalities

4.2.1 ON/OFF


An output can be switched on or off using the ON/OFF function. The command can come from switches, buttons or other control inputs.

- **ON**: switches the lighting circuit on.




Closing input contact: turns on the light at the last saved level Opening input contact: no action

OFF: switches the lighting circuit off.




Closing input contact: turns off the light Opening input contact: no action

ON/OFF: switches the lighting circuit on or off(switch).



Closing input contact: turns on the light at the last saved level Opening input contact: turns off the light

- **Toggle switch**: inverses the lighting circuit status.




Closing input contact: toggles between turning on at the last saved level and turning off the light Successive closings inverse output contact status each time.



4.2.2 Relative or absolute dimming (Brightness value)


With relative dimming, the brightness value is raised or lowered with respect to the current brightness value. This is achieved, for example, by a long press on a sensor button. With absolute dimming, the brightness value to be achieved is set on the dimmer as a % value.

- Increase dimming/ON: increases the output level.




Brief closing of the input contact: turns on the light at the last saved level Prolonged closing of the input contact: increase in the brightness level

- **Decrease dimming/OFF**: decreases the output level.




Brief closing of the input contact: turns off the light Prolonged closing of the input contact: decrease in the brightness level

- **Increase/decrease dimming**: varies the light with a single push-button.



Brief closing of the input contact: turns on the light at the last saved level or turns off the light Prolonged closing of the input contact: increase or decrease in the lighting level


- **Dimming**: varies the light with a defined brightness value.




Closing input contact: turns on the light at the defined brightness value Opening input contact: no action



Note: At the time the connection is made, the brightness value must be defined for the contact closure input.



- **Dimming switch**: varies the light with two brightness values defined according to the opening and closing of the input contact.




Closing input contact: turns on the light at the 1 brightness value Opening input contact: turns on the light at the 2 brightness value

Note: At the time the connection is made, the brightness values must be defined for the contact closure input.





4.2.3 Dimmer and switch principle-



- 1 Switch ON speed (soft ON)
- 2 Switch OFF speed (soft OFF)

Parameter	Description	Value
Last known brightness value at switch On	On receipt of an ON command on the ON/OFF communication object, the output is set to the following value:	
	100%	Not active
	To the last brightness value	Active*
Switch ON speed (soft ON)	This parameter defines the switch ON speed for attaining the brightness value after input of an ON command.	0 *1h45m00s
Switch OFF speed (soft OFF)	This parameter defines the switch OFF speed for attaining brightness value 0% after input of an OFF command.	0 *1h45m00s
Minimum relative dimming value (1 - 50%)	This parameter specifies a minimum brightness value for the dimming.	1*50
Maximum relative dimming value (51-100%)	This parameter specifies a maximum brightness value for the dimming.	51 100 *



4.2.4 Timer


The Timer function is used to switch on a lighting circuit for a programmable period. The timer may be interrupted before expiry of the delay time. A programmable Cut-OFF pre-warning announces the end of the delay time by halving the present brightness value of the output.



Parameter	Description	Value
Timer duration	duration.	Not active, 1 s, 2 s, 3 s, 5 s, 10 s, 15 s, 20 s, 30 s, 45 s, 1 min, 1 min 15 s, 1 min 30 s, 2 min*, 2 min 30 s, 3 min, 5 min, 15 min, 20 min, 30 min, 1 h, 2 h, 3 h, 5 h, 12 h, 24 h

Parameter	Description	Value
Cut-OFF pre-warning	This parameter determines the lead time of the cut-OFF pre-warning.	Not active, 15 s, 30 s* , 1 min

Operating principle:




Tm: Timer duration
Tp: Pre-warning lead time

Note: If the lead time of the cut-OFF pre-warning is greater than the duration of the timer, the cut-OFF pre-warning is not triggered.



- The connection:

The Timer function is used to switch on a lighting circuit for a programmable period.



Brief closing of the input contact: timing function light switched on at the last saved level

Timing function interruption:

Prolonged closing of the input contact: stop of timing delay in progress and light is turned off

Note: At the time of connection, it is possible to define the timer duration.





4.2.5 Priority


The Priority function is used to force the output into a defined state.

Priority: **Priority** > Basic function.

Only a Priority OFF command authorizes the output for control.


At the end of the priority, the output returns to the status it had before the priority (Memorisation function).

Operating principle:




Note: The brightness value for the ON priority corresponds to the last saved level.

- Links
 - **Priority ON**: allows forcing and keeping the lighting circuit on.



Closing input contact: turns on the light at the last saved level Opening input contact: end of the priority

- **Priority ON push-button**: allows forcing and keeping the light circuit on using a push-button.




Closing input contact: turns on the light at the last saved level Opening input contact: no action

A second closure of the input contact triggers the end of priority.




- Priority OFF: allows forcing and keeping the lighting circuit off.



Closing input contact: turns off the light Opening input contact: end of the priority

- **Priority OFF push-button**: allows forcing and keeping the lighting circuit off using a push-button.



Closing input contact: turns off the light Opening input contact: no action

A second closure of the input contact triggers the end of priority.




4.2.6 Automatic control

The Automatic control function is used to command an output in parallel to the ON/OFF function. The two functions have the same level of priority. The last command received will act on the status of the output. An additional command object is used to activate or deactivate the Automatic control.


Example: when an output is controlled by a button and in parallel by an automatic control (timer, twilight switch, weather station, etc.) the automatic control can be deactivated for reasons of comfort (vacations, public holidays, etc.).

Operating principle:



- Links


- Automatic control ON: allows turning on the light circuit using automatic control.



Closing input contact: turns on the light at the last saved level Opening input contact: no action




- Automatic control OFF: allows turning on the light circuit using automatic control.




Closing input contact: turns off the light Opening input contact: no action

- **ON/OFF automatic control**: allows turning the lighting circuit on or off using automatic control (switch).




Closing input contact: turns on the light at the last saved level Opening input contact: turns off the light

 Dimming automatic control PB: allows varying the light with a defined brightness value using automatic control.




Closing input contact: turns on the light at the last saved level Opening input contact: turns off the light

Note: At the time the connection is made, the brightness value must be defined for the contact closure input.



- **Dimmer switch automatic control**: allows varying the light with two defined brightness values according to the opening and closing input contact using automatic control.




Closing input contact: turns on the light at the 1 brightness value Opening input contact: turns on the light at the 2 brightness value



Note: At the time the connection is made, the brightness values must be defined for the contact closure input.




- Automatic control deactivation: deactivates automatic control.



Closing input contact: deactivated automatic control Opening input contact: activated automatic control

- Automatic control deactivation toggle: deactivates automatic control using a push-button.



Closing input contact: deactivated automatic control

Opening input contact: no action


A second closing input contact triggers activation of the automatic control.



4.2.7 Scene

The Scene function is used to switch groups of outputs into a configurable predefined state. Each output can be included in 8 different scenes.

Operating principle:



Learning and storing scenes

This process is used to change and store a scene. For example, by locally pressing the key in the room or by emission of the values from a visualization.


To access and store scenes, the following values must be sent:

Scene number	Access scene (Object value: 1 byte)	Store scene (Object value: 1 byte)
1-64	= Scene number -1	= Scene number +128
Examples		
1	0	128
2	1	129
3	2	130
64	63	191



Here is the scene memorisation for local switches, for example.


- Activate scene by briefly pressing the transmitter that starts it.
- The outputs (lights, shutters, etc.) are set in the desired state using the usual local control devices (buttons, remote control, etc.).
- Memorise the status of the outputs with a press greater than 5 seconds long on the transmitter that starts the scene. The memorisation can be displayed by short-term activation of the outputs.



Product learning and memorisation

This procedure allows modifying a scene using a local action on the push buttons located on the front side of the product.

- Activate the scene using a short press on the ambiance push button, which triggers the scene,
- Set the dimmer to Manual mode and set the outputs to the desired setting by pressing the appropriate output push-buttons,
- Return to Auto mode,
- Save the scene using a long push for more than 5 seconds on the push-button that triggers the scene,
- Memorisation is signalled by the inversion of the concerned output status for 3 sec.
- Links
 - **Scene**: the scene is activated by pressing the push-button.




Closing input contact: scene activation Opening input contact: no action

Note: At the time the connection is made, the scene number must be defined for the closing input contact.





- Scene switch: the scene is activated according to the closing or opening input contact.



Closing input contact: scene activation 1 Opening input contact: scene activation 2

Note: At the time the connection is made, the scene number must be defined for the closing and opening input contact.




4.2.8 Colour

The product supports control of the DALI "Colour Control" (DALI Device Type 8) equipment. Using appropriate DALI equipment and lighting sources enables the colour of a RGB(W) LED lamp to be controlled.

Scrolling colours allows you to select a pre-defined colour to be applied to the output. In addition to white, the available color set is as follows:




- Forward colour scrolling: enables clockwise colour scrolling.



Prolonged closing of the input contact: forward colour scrolling



- Rearward colour scrolling: enables anti-clockwise colour scrolling.




Prolonged closing of the input contact: rearward colour scrolling

4.2.9 Colour temperature


The product supports the control of the "Colour Control" DALI equipment (DALI Device Type 8) in the specific character "Tunable White (TW)". Using appropriate DALI equipment and lighting sources enables the colour temperature of a lamp to be controlled.

- Colour temperature increase: enables the colour temperature to be increased.



Prolonged closing of the input contact: colour temperature increase Opening input contact: no action

- Colour temperature decrease: enables the colour temperature to be decreased.



Prolonged closing of the input contact: colour temperature decrease Opening input contact: no action



5 Appendix

5.1 Specifications

Mains supply	
Supply voltage via mains	230 V~, + 10%/-15 %
	240 V~, +/-6%
Network frequency	50 / 60 Hz
Typical consumption	900 mW
KNX	
Supply voltage KNX	20 30 V SELV
Consumption on the KNX bus:	
- typical	2.35 mA
- in standby	1,7 mA
DALI	
Supply voltage DALI	16 V SELV
Guaranteed current	185 mA
Maximum current	250 mA
Start up time	< 500 ms
Ambient conditions	
Operating temperature	-5+ 45°C
Storage temperature	- 20+ 70°C
Ambient conditions	95% (20°C)
Pollution degree	2
Degree of protection of housing	IP20
Degree of protection of housing under front panel	IP30
IK (impact protection)	4
Operating altitude	2000 m max.
Surge voltage	4 kV
Circuit breaker protection	10 A
Box	
Footprint	108 mm / 6 modules
Output connection	
Connection capacity	0.75 mm ² 2.5 mm ²
DALI cable length:	
- Ø 1,5 mm²	300 m max.
- Ø 1,0 mm²	224 m max.
- Ø 0,75 mm²	168 m max.

5.2 Characteristics

Device	TXA664D
Max. number of group addresses	254
Max. number of allocations	255
Objects	151

